

## Screw connection - WP-G HF IP69K M40 BK - 3240887

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable gland, metric thread, IP68/69k protection, straight



### Key Commercial Data

Packing unit	1 STK
Minimum order quantity	25 STK
GTIN	 4 046356 709941
GTIN	4046356709941
Weight per Piece (excluding packing)	57.600 g
Custom tariff number	39174000
Country of origin	Germany

### Technical data

#### Dimensions

Width (a)	58 mm
Height (c)	76 mm
Wrench size	55 mm
Outside diameter	42.5 mm
Cable diameter	42.5 mm ... 42.5 mm

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 115 °C
Degree of protection	IP68/IP69K

#### General

# Screw connection - WP-G HF IP69K M40 BK - 3240887

## Technical data

### General

Color	black
Type	Straight
	Outer thread
Components	free from silicone, halogen, and cadmium
Flammability rating according to UL 94	V0
Material	PA

### Standards and Regulations

Resistance to UV radiation	no
Halogen-free	yes
Connection in acc. with standard	UL
Flammability rating according to UL 94	V0

### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

## Classifications

### eCl@ss

eCl@ss 4.0	27141131
eCl@ss 4.1	27141131
eCl@ss 5.0	27141131
eCl@ss 5.1	27141100
eCl@ss 7.0	27149109
eCl@ss 8.0	27149109
eCl@ss 9.0	27144432

### ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC001178
ETIM 5.0	EC001178
ETIM 6.0	EC000441

### UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411

# Screw connection - WP-G HF IP69K M40 BK - 3240887

## Classifications

### UNSPSC

UNSPSC 13.2	39121311
-------------	----------

## Approvals


### Approvals


#### Approvals


UL Recognized / VDE Zeichengenehmigung / LR

#### Ex Approvals

## Approval details

UL Recognized		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>
---------------	--	---

VDE Zeichengenehmigung		<a href="http://www2.vde.com/de/Institut/Online-Service/VDE-gepruefteProdukte/Seiten/Online-Suche.aspx">http://www2.vde.com/de/Institut/Online-Service/VDE-gepruefteProdukte/Seiten/Online-Suche.aspx</a>
------------------------	---	---

LR		<a href="http://www.lr.org/en">http://www.lr.org/en</a>
----	---	---

## Accessories

### Accessories

#### Corrugated pipe

Protective hose - WP-PA HF 42,5 BK - 3241089



Polyamide protective hose, inflammability class V0, UV resistant, 1 Pcs. / Pkt. = roll à 25 m

## Screw connection - WP-G HF IP69K M40 BK - 3240887

### Accessories

Protective hose - WP-PA HF-HB 42,5 BK - 3240844



Polyamide protective hose, inflammability class HB, UV resistant

---

### Mounting material

Protective hose fixing bracket - WP-BASE A M40 - 3241087



Fixing bracket for protective sleeves, fixed with two screws