

Screw connection - WP-GA HF IP69K PG16 BK - 3240905

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable gland, Pg thread, IP68/69k protection, angled

The figure shows the WP-GA HF IP69K M10 BK version

Key Commercial Data

Packing unit	1 pc
Minimum order quantity	50 pc
Weight per Piece (excluding packing)	18.4 g
Custom tariff number	39174000
Country of origin	Germany

Technical data

Dimensions

Length (b)	48 mm
Width (a)	29.5 mm
Height	50 mm
Diameter	27.00 mm
Outside diameter	21.20 mm
Cable diameter	21.2 mm ... 21.2 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 115 °C
Degree of protection	IP68/IP69K

General

Color	black
Type	Angled
	Outer thread
Components	free from silicone, halogen, and cadmium
Flammability rating according to UL 94	HB

Screw connection - WP-GA HF IP69K PG16 BK - 3240905

Technical data

General

Material	PA
----------	----

Standards and Regulations

Connection in acc. with standard	UL
Flammability rating according to UL 94	HB

Classifications

eCl@ss

eCl@ss 4.0	27141131
eCl@ss 4.1	27141131
eCl@ss 5.0	27141131
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27149109

ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC001178
ETIM 5.0	EC001178

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411

Approvals

Approvals

Approvals

UL Recognized / VDE Zeichengenehmigung / LR


Ex Approvals


Screw connection - WP-GA HF IP69K PG16 BK - 3240905

Approvals

Approvals submitted

Approval details

UL Recognized 

VDE Zeichengenehmigung 

LR
