

Screw connection - WP-GA HF IP69K M16 BK - 3240911

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable gland, metric thread, IP68/69k protection, angled



Key Commercial Data

Packing unit	1 STK
Minimum order quantity	50 STK
GTIN	 4 046356 710183
GTIN	4046356710183
Weight per Piece (excluding packing)	10.800 g
Custom tariff number	39174000
Country of origin	Germany

Technical data

Dimensions

Length (b)	40.5 mm
Width (a)	23 mm
Height (c)	42 mm
Diameter	24.5 mm
Outside diameter	15.8 mm
Cable diameter	15.8 mm ... 15.8 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 115 °C
Degree of protection	IP68/IP69K

Screw connection - WP-GA HF IP69K M16 BK - 3240911

Technical data

General

Color	black
Type	Angled
	Outer thread
Components	free from silicone, halogen, and cadmium
Flammability rating according to UL 94	HB
Material	PA

Standards and Regulations

Halogen-free	yes
Connection in acc. with standard	UL
Flammability rating according to UL 94	HB

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 4.0	27141131
eCl@ss 4.1	27141131
eCl@ss 5.0	27141131
eCl@ss 5.1	27141100
eCl@ss 7.0	27149109
eCl@ss 8.0	27149109
eCl@ss 9.0	27144432

ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC001178
ETIM 5.0	EC001178
ETIM 6.0	EC000441

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121311

Screw connection - WP-GA HF IP69K M16 BK - 3240911

Approvals

Approvals


Approvals


UL Recognized / VDE Zeichengenehmigung / LR

Ex Approvals

Approval details

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm
---------------	---	---

VDE Zeichengenehmigung		http://www2.vde.com/de/Institut/Online-Service/VDE-gepruefteProdukte/Seiten/Online-Suche.aspx
------------------------	--	---

LR		http://www.lr.org/en
----	---	---

Accessories

Accessories

Corrugated pipe

Protective hose - WP-PA HF 15,8 BK - 3240682



Polyamide protective hose, inflammability class V0, UV resistant

Screw connection - WP-GA HF IP69K M16 BK - 3240911

Accessories

Protective hose - WP-PA HF-HB 15,8 BK - 3240840



Polyamide protective hose, inflammability class HB, UV resistant

Mounting material

Protective hose fixing bracket - WP-BASE A M16 - 3241083



Fixing bracket for protective sleeves, fixed with two screws