

Transition sleeve from hose to cable - WP-EC TPE HF 10,0 BK - 3240974


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



End sleeves, transition sleeves, from hose to cable



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	50 pc
GTIN	 4 046356 710923
GTIN	4046356710923
Weight per Piece (excluding packing)	1.600 g
Custom tariff number	39174000
Country of origin	Germany

Technical data

Dimensions

Length (b)	29 mm
Diameter	10 mm
Outside diameter	10 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Short-term temperature	150 °C

General

Color	black
Components	halogen-free

Transition sleeve from hose to cable - WP-EC TPE HF 10,0 BK - 3240974

Technical data

General

Flammability rating according to UL 94	HB
Material	TPE

Standards and Regulations

Connection in acc. with standard	UL
Flammability rating according to UL 94	HB

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 10.0.1	27430316
eCl@ss 4.1	27141100
eCl@ss 5.1	27141100
eCl@ss 6.0	27141100
eCl@ss 7.0	27439210
eCl@ss 8.0	27439210
eCl@ss 9.0	27430316

ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC002584
ETIM 5.0	EC000519
ETIM 6.0	EC000519
ETIM 7.0	EC000519

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121404

Approvals

Approvals

Transition sleeve from hose to cable - WP-EC TPE HF 10,0 BK - 3240974

Approvals

Approvals

UL Recognized

Ex Approvals

Approval details

UL Recognized



<http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm>
