

Screw connection - WP-G PP HF PG21 - 3240992


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable gland made from PP with Pg thread, IP65 protection



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 046356 711241
GTIN	4046356711241
Weight per Piece (excluding packing)	24.000 g
Custom tariff number	39174000
Country of origin	Germany

Technical data

Dimensions

Width (a)	44 mm
Height (c)	48 mm
Wrench size	36 mm
Outside diameter	27 mm
Cable diameter	19.5 mm ... 19.5 mm

Ambient conditions

Ambient temperature (operation)	-10 °C ... 110 °C
Degree of protection	IP65

General

Screw connection - WP-G PP HF PG21 - 3240992

Technical data

General

Color	gray
Type	Straight
	Outer thread
Components	halogen-free
Flammability rating according to UL 94	HB
Material	PP

Standards and Regulations

Halogen-free	yes
Flammability rating according to UL 94	HB

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 4.0	27141131
eCl@ss 4.1	27141131
eCl@ss 5.0	27141131
eCl@ss 5.1	27141100
eCl@ss 6.0	27149100
eCl@ss 7.0	27149109
eCl@ss 8.0	27149109
eCl@ss 9.0	27144432

ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC001178
ETIM 5.0	EC001178
ETIM 6.0	EC000441
ETIM 7.0	EC000441

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411

Screw connection - WP-G PP HF PG21 - 3240992

Classifications

UNSPSC

UNSPSC 13.2	39121311
-------------	----------

Approvals


Approvals

Approvals

VDE Zeichengenehmigung

Ex Approvals

Approval details

VDE Zeichengenehmigung		http://www2.vde.com/de/Institut/Online-Service/VDE-gepruefteProdukte/Seiten/Online-Suche.aspx
------------------------	--	---

Accessories

Accessories

Corrugated pipe

Protective hose - WP-SPIRAL PVC C 27 - 3240853



Protective hose, spring steel wire with PVC coating, highly stranded

Protective hose - WP-SPIRAL PU C HF 27 - 3240860



Protective hose, spring steel wire with PU coating, highly stranded

Mounting material

Screw connection - WP-G PP HF PG21 - 3240992

Accessories

Protective hose fixing bracket - WP-BASE A PG21 - 3241080



Fixing bracket for protective sleeves, fixed with two screws