

Screw connection - WP-G PP HF M32 - 3241000

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable gland made from PP with metric thread, IP65 protection

Image shows WP-CG PP HF M10 version

Key Commercial Data

Packing unit	1 pc
Minimum order quantity	2 pc
Weight per Piece (excluding packing)	30.0 g
Custom tariff number	39174000
Country of origin	Germany

Technical data

Dimensions

Width (a)	54 mm
Height	51 mm
Wrench size	45.00 mm
Outside diameter	36.00 mm
Cable diameter	27 mm ... 27 mm

Ambient conditions

Ambient temperature (operation)	-10 °C ... 110 °C
Degree of protection	IP65

General

Color	gray
Type	Straight
	Outer thread
Components	Halogen-free
Flammability rating according to UL 94	HB
Material	PP

Screw connection - WP-G PP HF M32 - 3241000

Technical data

Standards and Regulations

Flammability rating according to UL 94	HB
--	----

Classifications

eCl@ss

eCl@ss 4.0	27141131
eCl@ss 4.1	27141131
eCl@ss 5.0	27141131
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27149109

ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC001178
ETIM 5.0	EC001178

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411

Approvals

Approvals

Approvals

VDE Zeichengenehmigung

Ex Approvals

Approvals submitted

Screw connection - WP-G PP HF M32 - 3241000

Approvals

Approval details

