

Cable protection end sleeve - WP-SC HF 27 - 3241020

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



End sleeves as cable protection

Image shows WP-TS HF 10 version

Key Commercial Data

Packing unit	1 pc
Minimum order quantity	25 pc
Weight per Piece (excluding packing)	2.4 g
Custom tariff number	39174000
Country of origin	Germany

Technical data

Dimensions

Diameter	27.00 mm
Inner diameter (f)	21.00 mm

Ambient conditions

Ambient temperature (operation)	-10 °C ... 110 °C
---------------------------------	-------------------

General

Color	gray
Components	Halogen-free
Flammability rating according to UL 94	HB
Material	PP

Standards and Regulations

Flammability rating according to UL 94	HB
--	----

Cable protection end sleeve - WP-SC HF 27 - 3241020

Classifications

eCl@ss

eCl@ss 4.0	27141131
eCl@ss 4.1	27141131
eCl@ss 5.0	27141131
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27439210

ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC002584
ETIM 5.0	EC000519

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411