

## Screw connection - WP-GT BRASS M10 - 3241030


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable gland made from brass with metric thread, rotatable, IP40 protection



### Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 046356 711661
GTIN	4046356711661
Weight per Piece (excluding packing)	14.000 g
Custom tariff number	74122000
Country of origin	Germany

### Technical data

#### Dimensions

Length (b)	32 mm
Width (a)	17 mm
Height (c)	32 mm
Wrench size	15 mm
Inner diameter (f)	6 mm
Outside diameter	10 mm

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 250 °C
Degree of protection	IP40

## Screw connection - WP-GT BRASS M10 - 3241030

### Technical data

#### General

Color	brass
Type	Rotatable
	Outer thread
Components	halogen-free
Material	Brass

### Classifications

#### eCl@ss

eCl@ss 4.0	27141209
eCl@ss 4.1	27141209
eCl@ss 5.0	21132007
eCl@ss 5.1	21132000
eCl@ss 6.0	21132000
eCl@ss 7.0	27439203
eCl@ss 8.0	27439203
eCl@ss 9.0	27430310

#### ETIM

ETIM 3.0	EC000519
ETIM 4.0	EC000519
ETIM 5.0	EC001180
ETIM 6.0	EC001180
ETIM 7.0	EC001180

#### UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	40141734

### Approvals

#### Approvals

---

#### Approvals

VDE Zeichengenehmigung

## Screw connection - WP-GT BRASS M10 - 3241030

### Approvals

---

Ex Approvals

---

### Approval details

VDE Zeichengenehmigung



<http://www2.vde.com/de/Institut/Online-Service/VDE-gepruefteProdukte/Seiten/Online-Suche.aspx>

### Accessories

#### Accessories

##### Corrugated pipe

Protective hose - WP-STEEL ZC 10 - 3240697



Protective hose in galvanized steel

---

Protective hose - WP-STEEL S 10 - 3240686



Protective hose in stainless steel

---