

Screw connection - WP-G BRASS IP40 M10 - 3241044

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable gland made from brass with metric thread, IP40 protection

RoHS

Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 046356 711807
GTIN	4046356711807
Weight per Piece (excluding packing)	14.000 g
Custom tariff number	74122000
Country of origin	Germany

Technical data

Dimensions

Length (b)	31 mm
Width (a)	19 mm
Height (c)	31 mm
Wrench size	15 mm
Inner diameter (f)	6 mm
Outside diameter	10 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
Degree of protection	IP40

Screw connection - WP-G BRASS IP40 M10 - 3241044

Technical data

General

Color	brass
Type	Straight
	Outer thread
Components	halogen-free
Material	Brass

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Classifications

eCl@ss

eCl@ss 10.0.1	27430310
eCl@ss 4.0	27141200
eCl@ss 4.1	27141200
eCl@ss 5.0	21132000
eCl@ss 5.1	21132000
eCl@ss 6.0	21132000
eCl@ss 7.0	27439203
eCl@ss 8.0	27439203
eCl@ss 9.0	27430310

ETIM

ETIM 3.0	EC000519
ETIM 4.0	EC000519
ETIM 5.0	EC001180
ETIM 6.0	EC001180
ETIM 7.0	EC001180

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	40141734
UNSPSC 18.0	40141734
UNSPSC 19.0	40141734
UNSPSC 20.0	40141734

Screw connection - WP-G BRASS IP40 M10 - 3241044

Classifications

UNSPSC

UNSPSC 21.0	40141734
-------------	----------

Approvals

Approvals

Approvals

VDE Zeichengenehmigung

Ex Approvals

Approval details

VDE Zeichengenehmigung		http://www2.vde.com/de/Institut/Online-Service/VDE-gepruefteProdukte/Seiten/Online-Suche.aspx
------------------------	--	---

Accessories

Accessories

Corrugated pipe

Protective hose - WP-STEEL ZC 10 - 3240697



Protective hose in galvanized steel

Protective hose - WP-STEEL S 10 - 3240686



Protective hose in stainless steel

