

Screw connection - WP-G BRASS IP65 PG11 - 3241053

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable gland made from brass with Pg thread, IP65 protection

The figure shows the WP-G BRASS
IP65 M10 version

Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
Weight per Piece (excluding packing)	30.0 g
Custom tariff number	74122000
Country of origin	Germany

Technical data

Dimensions

Width (a)	27 mm
Height	30 mm
Wrench size	23.00 mm
Outside diameter	17.00 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
Degree of protection	IP65

General

Color	Brass
Type	Straight
	Outer thread
Components	Halogen-free
Material	Brass

Screw connection - WP-G BRASS IP65 PG11 - 3241053

Classifications

eCl@ss

eCl@ss 4.0	27141209
eCl@ss 4.1	27141209
eCl@ss 5.0	21132007
eCl@ss 5.1	21132007
eCl@ss 6.0	21132007
eCl@ss 7.0	27439210
eCl@ss 8.0	27439203

ETIM

ETIM 3.0	EC000519
ETIM 4.0	EC000519
ETIM 5.0	EC001180

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411

Approvals

Approvals


Approvals

VDE Zeichengenehmigung

Ex Approvals

Approvals submitted

Approval details

VDE Zeichengenehmigung 
--

