

Spiral tube - WG-S HF 70 - 3241117

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Spiral hose, for easy bundling and guiding of cables and conductors, offers protection against slight mechanical strain

The figure shows a version of the article

Key Commercial Data

Packing unit	1 pc
Minimum order quantity	25 pc
Weight per Piece (excluding packing)	99.0 g
Custom tariff number	39269097
Country of origin	Poland

Technical data

Dimensions

Length (b)	25 m
Width (a)	70 mm
Cable diameter	13 mm ... 70 mm

Ambient conditions

Ambient temperature (operation)	-50 °C ... 85 °C
Ambient temperature (assembly)	-20 °C ... 60 °C

General

Color	transparent
Type	Continuous strip
Components	free from silicone and halogen
Flammability rating according to UL 94	HB
Material	PE

Standards and Regulations

Flammability rating according to UL 94	HB
--	----

Spiral tube - WG-S HF 70 - 3241117

Classifications

eCl@ss

eCl@ss 4.0	27140602
eCl@ss 4.1	27140602
eCl@ss 5.0	27140602
eCl@ss 5.1	27140602
eCl@ss 6.0	27400703
eCl@ss 7.0	27400703
eCl@ss 8.0	27430302

ETIM

ETIM 3.0	EC000012
ETIM 4.0	EC000046
ETIM 5.0	EC002604

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121411
UNSPSC 11	39121411
UNSPSC 12.01	39121708
UNSPSC 13.2	39121411