

Covering hood - HC-RBO 12 - 3247983

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Covering hood, length: 164 mm, width: 49 mm, height: 33 mm, color: gray

RoHS

Key Commercial Data

| | |
|--------------------------------------|---|
| Packing unit | 1 STK |
| Minimum order quantity | 6 STK |
| GTIN |  4 046356 586399 |
| GTIN | 4046356586399 |
| Weight per Piece (excluding packing) | 40.000 g |
| Custom tariff number | 85389099 |
| Country of origin | China |

Technical data

General

| | |
|--|------|
| Color | gray |
| Material | PA |
| Flammability rating according to UL 94 | V0 |

Dimensions

| | |
|--------|--------|
| Width | 49 mm |
| Length | 164 mm |
| Height | 33 mm |

Standards and Regulations

| | |
|--|----|
| Flammability rating according to UL 94 | V0 |
|--|----|

Covering hood - HC-RBO 12 - 3247983

Technical data

Environmental Product Compliance

| | |
|------------|---|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
| | No hazardous substances above threshold values |

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 5.1 | 27141143 |
| eCl@ss 6.0 | 27379200 |
| eCl@ss 8.0 | 27141190 |
| eCl@ss 9.0 | 27141190 |

ETIM

| | |
|----------|----------|
| ETIM 5.0 | EC002848 |
| ETIM 6.0 | EC002848 |

UNSPSC

| | |
|-------------|----------|
| UNSPSC 13.2 | 39121410 |
|-------------|----------|

Approvals


Approvals

Approvals

EAC

Ex Approvals

Approval details

| | | |
|-----|---|---------------|
| EAC |  | EAC-Zulassung |
|-----|---|---------------|