

Cover profile - APK-TU - 5022805

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Cover profile holder, 10 mm wide, for mounting on NS 32 or NS 35/7.5, for fixing the holding profile APK-HP, labeling with Zack strip ZB 10

Product Features

- Can be labeled
- Protection against accidental actuation of terminal points or disconnect terminal blocks
- Protection against environmental influences
- Covering of live parts



Key commercial data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 017918 095307
Weight per Piece (excluding packing)	9.01 GRM
Custom tariff number	39269097
Country of origin	Germany

Technical data

Dimensions

Width (a)	10 mm
-----------	-------

Ambient conditions

Ambient temperature (operation)	-40 °C ... 115 °C
---------------------------------	-------------------

General

Color	gray
Components	free from silicone and halogen

Cover profile - APK-TU - 5022805

Technical data

General

Inflammability class according to UL 94	V2
Material	PA

Classifications

eCl@ss

eCl@ss 4.0	23150301
eCl@ss 4.1	23150301
eCl@ss 5.0	27141143
eCl@ss 5.1	27141143
eCl@ss 6.0	27379200
eCl@ss 7.0	27141143
eCl@ss 8.0	27141143

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC002498
ETIM 5.0	EC000886

UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	39121708
UNSPSC 11	39121708
UNSPSC 12.01	39121708
UNSPSC 13.2	39121708

Drawings

Cover profile - APK-TU - 5022805

