

Label sheet, DIN A4 - BMKL 25X 8 WH



5032332

<https://www.phoenixcontact.com/us/products/5032332>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.

Label sheet, DIN A4, Sheet, white, unlabeled, can be labeled with: PLOTMARK, CMS-P1-PLOTTER, Office printing systems, mounting type: adhesive, lettering field size: 25 x 8 mm, Number of individual labels: 224



Your advantages

- These labels have been specially developed for laser printers
- Labeling service: Phoenix Contact can custom-label all BMKL ... markers according to your requirements
- Can be printed on all commercially available laser printers
- The material file can be downloaded under the CLIP PROJECT software under Downloads - "Software update - Marking"
- The unperforated SK-U... sheets are available for custom label designs

Commercial Data

| | |
|--------------------------------------|--------------------------------|
| Item number | 5032332 |
| Packing unit | 1 pc |
| Minimum order quantity | 10 pc |
| Note | Made to Order (non-returnable) |
| Sales Key | B12 |
| Product Key | BG2414 |
| Catalog Page | Page 344 (C-3-2019) |
| GTIN | 4017918095758 |
| Weight per Piece (including packing) | 15.16 g |
| Weight per Piece (excluding packing) | 15.16 g |
| Customs tariff number | 39199080 |
| Country of origin | DE |

Technical Data

Product properties

| | |
|--------------|----------------|
| Product type | Device marking |
|--------------|----------------|

Marking

| | |
|-------------------------------------|-----|
| Number of individual labels | 224 |
| Number of individual labels per row | 7 |

Mounting

| | |
|---------------|----------|
| Mounting type | adhesive |
|---------------|----------|

Material specifications

| | |
|-----------------------|---------------|
| Color | white |
| Material | Polyester |
| Base element material | Polyester |
| Components | Silicone-free |

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

| | |
|--------|--------------------|
| | VDMA 24364:2018-05 |
| Result | Test passed |

Scratch test for the determining scratch resistance

| | |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 1518-1:2019-10 (following) |
| Requirements | ≥ 5 N |
| Result | Test passed |

Tesafilm test

| | |
|---------------|----------------------------------|
| Specification | DIN EN ISO 2409:2013 (following) |
| Result | Test passed |

UV resistance

| | |
|---------------|--------------------------------|
| Specification | ISO 4892-2:2013-03 (following) |
| Result | Test passed |
| Test duration | 96 h |

Temperature resistance

| | |
|------------------------|---------------------------------|
| Specification | ANSI/UL 969-2018:03 (following) |
| Test duration | 240 h |
| Rating 200 °C (230 °C) | Test passed |
| Specification | ISO 175:2010 (following) |
| Test duration | 168 h |

Testing in a condensation changing climate in the presence of sulfur dioxide

| | |
|---------------|-------------------|
| Specification | DIN 50018:2013-05 |
|---------------|-------------------|

Label sheet, DIN A4 - BMKL 25X 8 WH



5032332

<https://www.phoenixcontact.com/us/products/5032332>

| | |
|---------------|-------------|
| Result | Test passed |
| Climate level | AHT 1.0 S |
| Cycles | 2 |

Salt spray test

| | |
|---------------|---------------------------|
| Specification | DIN EN 60068-2-11:2000-02 |
| Result | Test passed |
| Test duration | 96 h |

Ambient conditions

| | |
|-----------------------------------------------------|------------------|
| Ambient temperature (operation) | -20 °C ... 80 °C |
| Recommended ambient temperature (storage/transport) | 20 °C ... 25 °C |
| Recommended humidity (storage/transport) | 40 % ... 50 % |

Dimensions

| | |
|--------|-------|
| Width | 25 mm |
| Length | 8 mm |

Standards and regulations

| | |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

Notes

| | |
|---------|-------------------------------------------------|
| General | Print image may vary depending on laser printer |
|---------|-------------------------------------------------|

Label sheet, DIN A4 - BMKL 25X 8 WH



5032332

<https://www.phoenixcontact.com/us/products/5032332>

Classifications

ECLASS

| | |
|---------------|----------|
| ECLASS-9.0 | 27400629 |
| ECLASS-11.0 | 27281103 |
| ECLASS-10.0.1 | 27400629 |

ETIM

| | |
|----------|----------|
| ETIM 8.0 | EC001288 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

Label sheet, DIN A4 - BMKL 25X 8 WH



5032332

<https://www.phoenixcontact.com/us/products/5032332>

Accessories

Accessories

Accessories - CMS-P1-PAD - 5144819

<https://www.phoenixcontact.com/us/products/5144819>



Accessories

Phoenix Contact 2023 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com