

## Marker pin Zack strip - BN-ZB 6,2/WH-100:UNBEDRUCKT - 5060867


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Marker pin Zack strip, Strip, white, unlabeled, can be labeled with: Plotter, Mounting type: Plug in, for terminal block width: 6.2 mm, Lettering field: 4 x 4 mm

The illustration shows version BN-ZB 6,2 -UNPRINTED, - CONSEC. NOS and BNB-ZB 6,2 SO/CMS

### Key Commercial Data

Packing unit	1 STK
Minimum order quantity	100 STK
GTIN	 4 017918 096090
GTIN	4017918096090
Weight per Piece (excluding packing)	0.290 g
Custom tariff number	39269097
Country of origin	Germany

### Technical data

#### Dimensions

Width (a)	4 mm
-----------	------

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
---------------------------------	-------------------

#### General

Note	Can be labeled with CMS
Color	white
Components	free from silicone and halogen
Flammability rating according to UL 94	V2
Material	PA
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	1000

## Marker pin Zack strip - BN-ZB 6,2/WH-100:UNBEDRUCKT - 5060867

### Technical data

#### General

Marking mounting type	Plug in
-----------------------	---------

#### Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Flammability rating according to UL 94	V2