

Cable - CAB-TE MR24F/OE/24/S/ 1M - 2909746

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Why buy this product

- Individual wire marking: 1, 2, 3, 4, etc.
- Individual wires fitted with ferrules
- Screw connection: 2 UNC 4-40 screws
- Open end at one end
- D-SUB socket or pin strip at one end
- 1:1 connection

Key Commercial Data

Packing unit	1 STK
Weight per Piece (excluding packing)	200.000 g
Country of origin	United States

Technical data

General

Nominal voltage U_N	125 V AC
	125 V DC
Max. current carrying capacity per path	1 A
Length of cable	1 m
Single wire, cross section	0.25 mm ²
Single wire, cross section [AWG]	24
External diameter	9.4 mm
Shielding	yes
	Overall foil and braid shield

Environmental conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

Cable - CAB-TE MR24F/OE/24/S/ 1M - 2909746

Technical data

Supported controller

Controller	universal
------------	-----------

Color code

Connector 1 = connector 2 (optional) = wire color	MR24F (1) = black
	MR24F (2) = white
	MR24F (3) = red
	MR24F (4) = green
	MR24F (5) = orange
	MR24F (6) = blue
	MR24F (7) = white-black
	MR24F (8) = red-black
	MR24F (9) = green-black
	MR24F (10) = orange-black
	MR24F (11) = blue-black
	MR24F (12) = black-white
	MR24F (13) = red-white
	MR24F (14) = green-white
	MR24F (15) = blue-white
	MR24F (16) = black-red
	MR24F (17) = white-red
	MR24F (18) = orange-red
	MR24F (19) = blue-red
	MR24F (20) = red-green
	MR24F (21) = orange-green
	MR24F (22) = black-white-red
	MR24F (23) = white-black-red
	MR24F (24) = red-black-white

Classifications

eCl@ss

eCl@ss 7.0	27249205
eCl@ss 8.0	27249205
eCl@ss 9.0	27242220

ETIM

ETIM 5.0	EC000237
ETIM 6.0	EC000237

Cable - CAB-TE MR24F/OE/24/S/ 1M - 2909746

Accessories

Accessories

Marker carrier cable

Cable marker carrier - KME - 0807083



Cable marker carrier, white, unlabeled, mounting type: Assembly with cable binders, cable diameter: > 5 mm, lettering field size: 20 mm x 8 mm