

TMP-UM-MAG10 - Magazine

0803334

<https://www.phoenixcontact.com/nl/products/0803334>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Magazine for THERMOMARK CARD and THERMOMARK PRIME, to hold UM material (UM7-TM)



Commercial data

Item number	0803334
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG122Z
Product key	BG122Z
GTIN	4055626028156
Weight per piece (including packing)	400 g
Weight per piece (excluding packing)	99,99 g
Customs tariff number	84439990
Country of origin	DE

Technical data

Dimensions

Width	114 mm
Height	116 mm
Depth	11.5 mm

Material specifications

RoHS compliant	yes
----------------	-----

Environmental and real-life conditions

Ambient conditions

Recommended storage conditions	20 °C / 50 % relative humidity.
--------------------------------	---------------------------------

Classifications

ECLASS

ECLASS-13.0	19140615
ECLASS-15.0	19140615

ETIM

ETIM 9.0	EC001675
----------	----------

UNSPSC

UNSPSC 21.0	43211600
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	1,509 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT B.V.

Hengelder 56 6902 PA Zevenaar

Postbus 246 6900 AE Zevenaar

(0316) 59 17 20

sales@phoenixcontact.nl