

Support bracket - PTFIX 1,5-NS35AD - 1049498

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Support bracket, width: 8 mm



Key Commercial Data

Packing unit	30 pc
Minimum order quantity	30 pc
GTIN	 4 055626 650890
GTIN	4055626650890
Weight per Piece (excluding packing)	1.500 g
Custom tariff number	39269097
Country of origin	Poland

Technical data

General

Ambient temperature (operation)	-60 °C ... 85 °C
Ambient temperature (storage/transport)	-25 °C ... 55 °C (For a short time, not exceeding 24 h, -60 to +70 °C)
Moisture, minimum (storage/transport)	30 %
Moisture, maximum (storage/transport)	70 %
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C

Dimensions

Width	8 mm
-------	------

Classifications

eCl@ss

eCl@ss 10.0.1	27141190
---------------	----------

Support bracket - PTFIX 1,5-NS35AD - 1049498

Classifications

eCl@ss

eCl@ss 8.0	27370419
eCl@ss 9.0	27370419

ETIM

ETIM 5.0	EC001024
ETIM 6.0	EC001024
ETIM 7.0	EC001024

Approvals


Approvals


Approvals


EAC / CSA / cUL Recognized / UL Recognized / cULus Recognized

Ex Approvals

Approval details


EAC		RU C- DE.AI30.B.01102
-----	-------------------------------------------------------------------------------------	--------------------------

CSA		http://www.csagroup.org/services-industries/product-listing/	13631
	B	C	D
Nominal voltage UN	300 V	150 V	300 V
Nominal current IN	20 A	20 A	10 A
mm ² /AWG/kcmil	26-12	26-12	26-12

cUL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 60425
	B	C	D
Nominal voltage UN	300 V	150 V	300 V
Nominal current IN	15 A	15 A	10 A
mm ² /AWG/kcmil	26-14	26-14	26-14

Support bracket - PTFIX 1,5-NS35AD - 1049498

Approvals

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 60425
	B	C	D
Nominal voltage UN	300 V	150 V	300 V
Nominal current IN	20 A	20 A	10 A
mm ² /AWG/kcmil	26-12	26-12	26-12

cULus Recognized	
------------------	-----------------------------------------------------------------------------------