

SACC BIT M12-D23 - Tool

1202885

<https://www.phoenixcontact.com/nl/products/1202885>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Nut for assembling M12 connectors for assembly with a knurl diameter of 23 mm, for 4 mm hexagonal drive



The figure shows an example product from the product range

Commercial data

Item number	1202885
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH3149
Product key	BH3149
GTIN	4063151265663
Weight per piece (including packing)	21 g
Weight per piece (excluding packing)	21 g
Customs tariff number	82079030
Country of origin	DE

SACC BIT M12-D23 - Tool

1202885

<https://www.phoenixcontact.com/nl/products/1202885>



Technical data

Connection data

Output	QUICKON fast connection
--------	-------------------------

Dimensions

Width	25 mm
Height	6 mm
Length	25.7 mm

Material specifications

Material	alloyed tool steel
Coating	nickel-plated

SACC BIT M12-D23 - Tool

1202885

<https://www.phoenixcontact.com/nl/products/1202885>



Classifications

ECLASS

ECLASS-13.0	21045191
ECLASS-15.0	21045191

ETIM

ETIM 10.0	EC011822
-----------	----------

UNSPSC

UNSPSC 21.0	27111700
-------------	----------

SACC BIT M12-D23 - Tool



1202885
<https://www.phoenixcontact.com/nl/products/1202885>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT B.V.
Hengelder 56 6902 PA Zevenaar
Postbus 246 6900 AE Zevenaar
(0316) 59 17 20
sales@phoenixcontact.nl