

BL2 BPC 1541E-8/128-W10 - Box PC



1272687

<https://www.phoenixcontact.com/nl/products/1272687>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



IP30-rated fanless industrial box PC (BPC) with energy-efficient Intel® Atom® E3940 processor with 128 GB eMMC and Windows 10 Enterprise 2019 LTSC operating system.

Similar figure

Commercial data

Item number	1272687
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DRBABA
Product key	DRBABA
GTIN	4063151465001
Weight per piece (including packing)	920,8 g
Weight per piece (excluding packing)	746 g
Customs tariff number	84715000
Country of origin	TW

BL2 BPC 1541E-8/128-W10 - Box PC



1272687

<https://www.phoenixcontact.com/nl/products/1272687>

Technical data

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Product properties

Computer data

Processor	Intel® Atom™ E3940 1.6 GHz
Operating system	Windows® 10 IoT Enterprise LTSC 2019 (64-bit), Multi-language
RAM	8 GB LPDDR4
Data storage system	M.2 SSD, 128 GB
Cooling	passive

Display

Display type	none
--------------	------

System properties

User software	without user software
---------------	-----------------------

Electrical properties

Maximum power dissipation for nominal condition	16.8 W
---	--------

Supply

Supply voltage (DC)	24 V DC $\pm 20\%$ (CE rating)
Supply voltage range	12 V DC ... 30 V DC (Labeled operational voltage is 12 ... 30 V DC)
Max. current consumption	0.7 A (24 V DC)
Typical current consumption	0.53 A (24 V DC)

Connection data

Power supply

Connection method	Screw connection
Conductor cross-section, rigid	0.14 mm ² ... 1.5 mm ²
Conductor cross-section, flexible	0.14 mm ² ... 1.5 mm ²
Conductor cross-section AWG	28 ... 16
Stripping length	7 mm

Interfaces

Interfaces	1x DP++
	2x USB 3.0
	2x COM ports
Network	2x Ethernet (10/100/1000 Mbps), RJ45
LAN chipset	Intel® I210-AT

BL2 BPC 1541E-8/128-W10 - Box PC



1272687

<https://www.phoenixcontact.com/nl/products/1272687>

Dimensions

External dimensions

Width / Height / Depth	99 mm / 92 mm / 63 mm
------------------------	-----------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP30
	IP30
Ambient temperature (operation)	-20 °C ... 60 °C (with 0.5 m/s airflow)
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	5 % ... 85 % (non-condensing)
Shock	15g, 11 ms in accordance with IEC 60068-2-27
Vibration (operation)	1g, according to EN 60068-2-6

Approvals

Conformity/Approvals

Conformance	CE-compliant
-------------	--------------

Mounting

Mounting type	DIN rail mounting
	Panel mounting (Accessories required)

BL2 BPC 1541E-8/128-W10 - Box PC



1272687

<https://www.phoenixcontact.com/nl/products/1272687>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/nl/products/1272687>



IECEE CB Scheme

Approval ID: US-39601-M1-UL



UL Listed

Approval ID: E238705 D12:D1050



cUL Listed

Approval ID: E238705 D12:D1050

BL2 BPC 1541E-8/128-W10 - Box PC



1272687

<https://www.phoenixcontact.com/nl/products/1272687>

Classifications

ECLASS

ECLASS-13.0	19200102
ECLASS-15.0	19200102

ETIM

ETIM 9.0	EC001413
----------	----------

UNSPSC

UNSPSC 21.0	43211500
-------------	----------

1272687

<https://www.phoenixcontact.com/nl/products/1272687>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-15
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT B.V.
Hengelder 56 6902 PA Zevenaar
Postbus 246 6900 AE Zevenaar
(0316) 59 17 20
sales@phoenixcontact.nl