

BC 107,6 DKL R D2,4 TCG KMGY - Housing cover with touch display



1335858

<https://www.phoenixcontact.com/nl/products/1335858>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail housing for use in distribution boards in accordance with DIN 43880, Latching cover (non-detachable), integrated capacitive 2.4" touch display, resolution: 320 x 240 Pixel(s), interface: 4-wire SPI, width: 107.6 mm, height: 45 mm, depth: 13.5 mm

Your advantages

- Fast device development with integrated 2.4" touch display
- Suitable for different device requirements, thanks to housing versions with and without membrane keypad
- Coordinated housing, keypad, and display design
- Maximum flexibility with many combination options for the housing cover and upper parts
- Customization of membrane keypad via configurator

Commercial data

Item number	1335858
Packing unit	5 pc
Minimum order quantity	5 pc
Sales key	ACHBAI
Product key	ACHBAI
GTIN	4063151636593
Weight per piece (including packing)	51,86 g
Weight per piece (excluding packing)	43,84 g
Customs tariff number	85480090
Country of origin	CN

BC 107,6 DKL R D2,4 TCG KMGY - Housing cover with touch display



1335858

<https://www.phoenixcontact.com/nl/products/1335858>

Technical data

Notes

Assembly note	Please observe the application note in the download area.
Recommendation	Further information and detailed dimensions are available in the download area.
Order information:	Screws for mounting a PCB under the display are available as accessories, but are not included in the scope of delivery.

Product properties

Housing type	DIN rail housing for use in distribution boards in accordance with DIN 43880
Housing type	Modular building installation housings
Housing series	BC
Product family	BC 107,6..
Number (Connection openings)	0
Ventilation openings present	no

Display

Display type	TFT, IPS
Display type	capacitive
Diagonal	2.4 in. / 6.1 cm (Display)
Screen resolution	320 x 240 Pixel(s) (QVGA)
Display formats	3:4
Display lighting type	LED, white
Controller	GT911 (Goodix)

Interfaces

Interface	4-wire SPI
-----------	------------

Dimensions

Width	107.6 mm
Height	45 mm
Depth	13.5 mm

Material specifications

Color (Housing cover)	light gray (RAL 7035)
Material Housing cover	PC
Flammability rating according to UL 94	V0
Surface characteristics	untreated

PCB data

Type of PCB mount	Latching
-------------------	----------

BC 107,6 DKL R D2,4 TCG KMGY - Housing cover with touch display



1335858

<https://www.phoenixcontact.com/nl/products/1335858>

Mounting

Mounting type	Latching with upper housing part
---------------	----------------------------------

Packaging specifications

Type of packaging	Box packaging
-------------------	---------------

BC 107,6 DKL R D2,4 TCG KMGY - Housing cover with touch display



1335858

<https://www.phoenixcontact.com/nl/products/1335858>

Classifications

ECLASS

ECLASS-13.0	27190603
ECLASS-15.0	27190603

ETIM

ETIM 9.0	EC002779
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

BC 107,6 DKL R D2,4 TCG KMGY - Housing cover with touch display



1335858

<https://www.phoenixcontact.com/nl/products/1335858>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT B.V.
Hengelder 56 6902 PA Zevenaar
Postbus 246 6900 AE Zevenaar
(0316) 59 17 20
sales@phoenixcontact.nl