

SAC-3P-P12MR/ 0,6-PUR/P12FS - Sensor/actuator cable



1392254

<https://www.phoenixcontact.com/nl/products/1392254>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 3-position, PUR halogen-free, black-gray RAL 7021, Plug angled M12 Push Pull, coding: A, on Socket straight M12 Push Pull, coding: A, cable length: 0.6 m

Your advantages

- Easy and safe: 100 % electrically tested plug-in components
- Save time, thanks to installation with push-pull fast locking

Commercial data

Item number	1392254
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AF1CBC
Product key	AF1CBC
GTIN	4063151818814
Weight per piece (including packing)	42,9 g
Weight per piece (excluding packing)	43,435 g
Customs tariff number	85444290
Country of origin	PL

SAC-3P-P12MR/ 0,6-PUR/P12FS - Sensor/actuator cable



1392254

<https://www.phoenixcontact.com/nl/products/1392254>

Technical data

Product properties

Application	Standard
Number of positions	3
No. of cable outlets	1
Shielded	no
Coding	A

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Material	PK (Pin contact carrier) (Female connector contact carrier)
Flammability rating according to UL 94	V0
Seal material	FKM
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuSn
Contact surface material	Ni/Au
Material for screw connection	Brass, nickel-plated

Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	250 V AC 250 V DC
Nominal current I_N	4 A

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	------------

Signaling

Status display	no
Status display present	no

Connection data

Conductor connection

Tightening torque	M12 push-pull connectors
-------------------	--------------------------

Connector

Connection 1

SAC-3P-P12MR/ 0,6-PUR/P12FS - Sensor/actuator cable



1392254

<https://www.phoenixcontact.com/nl/products/1392254>

Type	Plug angled M12 Push Pull
Number of positions	3
Locking type	Push Pull
Coding type	A


Connection 2

Type	Socket straight M12 Push Pull
Number of positions	3
Locking type	Push Pull
Coding type	A

Cable/line

Cable length	0.6 m
--------------	-------

PUR halogen-free black [PUR]

Dimensional drawing	
Cable weight	23 kg/km
UL AWM Style	20549
Number of positions	3
Shielded	no
Cable type	PUR halogen-free black [PUR]
Conductor structure signal line	42x 0.10 mm
AWG signal line	22
Conductor cross-section	3x 0.34 mm ² (Signal line)
Wire diameter incl. insulation	1.27 mm ±0.02 mm (Signal line)
External cable diameter	3.85 mm ±0.15 mm
Outer sheath, material	PUR
External sheath, color	black-gray RAL 7021
Conductor material	Bare Cu litz wires
Material wire insulation	PP
Single wire, color	brown, blue, black
Thickness, insulation	≥ 0.21 mm (Core insulation) approx. 0.50 mm (Outer cable sheath)
Overall twist	3 wires, twisted
Max. conductor resistance	max. 58 Ω/km (at 20 °C)
Insulation resistance	≥ 100 GΩ*km (at 20 °C)
Nominal voltage, cable	≤ 300 V
Test voltage	≥ 3000 V

SAC-3P-P12MR/ 0,6-PUR/P12FS - Sensor/actuator cable



1392254

<https://www.phoenixcontact.com/nl/products/1392254>

Smallest bending radius, fixed installation	19 mm
Smallest bending radius, movable installation	38 mm
Dynamic load capacity (bending)	Max. bending cycles: 10000000, Bending radius: 38 mm, Bending radius: 10 x D, Traversing path: 10 m, Traversing rate: 3 m/s, Acceleration: 10 m/s ²
Dynamic load capacity (torsion)	Torsion: ± 180 °/m, Torsion cycles: ≥ 2000000 , Torsional frequency: 35 cycles/min.
Halogen-free	in accordance with DIN VDE 0472 part 815
Flame resistance	in accordance with UL 758/1581 FT2 DIN EN 60332-2-2 (20 s)
Resistance to oil	in accordance with DIN EN 60811-2-1
Other resistance	Highly resistant to acids, alkaline solutions and solvents hydrolysis and microbe resistant partly UV-resistant (in accordance with DIN EN ISO 4892-2-A)
Special properties	Flexible cable conduit capable Silicone-free Free of substances which would hinder coating with paint or varnish
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation) -25 °C ... 80 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65 IP67
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 85 °C (Plug / socket)

Standards and regulations

Standard designation	M12-Push-Pull
Standards/specifications	IEC 61076-2-010


SAC-3P-P12MR/ 0,6-PUR/P12FS - Sensor/actuator cable

1392254

<https://www.phoenixcontact.com/nl/products/1392254>


Drawings

Dimensional drawing



M12 push-pull male connector, angled

Dimensional drawing



M12 push-pull female connector, straight

SAC-3P-P12MR/ 0,6-PUR/P12FS - Sensor/actuator cable

1392254


<https://www.phoenixcontact.com/nl/products/1392254>

Schematic diagram



Pin assignment of M12 push-pull male, 3-pos., A-coded, view of male side

Schematic diagram



Pin assignment of M12 push-pull female, 3-pos., A-coded, view of female side

SAC-3P-P12MR/ 0,6-PUR/P12FS - Sensor/actuator cable

1392254

<https://www.phoenixcontact.com/nl/products/1392254>

Circuit diagram



Contact assignment of the M12 plug and the M12 socket

SAC-3P-P12MR/ 0,6-PUR/P12FS - Sensor/actuator cable



1392254
<https://www.phoenixcontact.com/nl/products/1392254>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/nl/products/1392254>

 cULus Listed Approval ID: E221474				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	300 V	4 A	- 22	-

SAC-3P-P12MR/ 0,6-PUR/P12FS - Sensor/actuator cable



1392254

<https://www.phoenixcontact.com/nl/products/1392254>

Classifications

ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

ETIM

ETIM 10.0	EC001855
-----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-3P-P12MR/ 0,6-PUR/P12FS - Sensor/actuator cable



1392254

<https://www.phoenixcontact.com/nl/products/1392254>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT B.V.
Hengelder 56 6902 PA Zevenaar
Postbus 246 6900 AE Zevenaar
(0316) 59 17 20
sales@phoenixcontact.nl