

HC-STA-B24-SLWD-2SSM25-ELC-AL - Housing



1412873

<https://www.phoenixcontact.com/nl/products/1412873>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Surface mounting housing B24, with double locking latch, material: Die-cast aluminum, salt water resistant, cable outlets: 2, lateral, 2x M25, height: 68 mm, cable gland: none, Standard

Your advantages

- Good shielding in the event of electromagnetic interference

Commercial data

Item number	1412873
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AF7APB
Product key	AF7APB
GTIN	4055626061221
Weight per piece (including packing)	360,1 g
Weight per piece (excluding packing)	352,138 g
Customs tariff number	85389099
Country of origin	PL

HC-STA-B24-SLWD-2SSM25-ELC-AL - Housing



1412873

<https://www.phoenixcontact.com/nl/products/1412873>

Technical data


Notes

General	for contact inserts HC-B24, BB46, D64, DD108, HV10/16, M
General	also available as a powder-coated or color version: 1372672 HC-STA-B24-SLWD-2SSM25-EL/.../...

Product properties

Housing type	Surface mounting housing
Application	Standard
Type	B24
No. of cable outlets	2
Type of the screw connection	2x M25
Cable outlet	lateral
Pg screw connection	none

Dimensions

Dimensional drawing	
Width	57 mm
Height	68 mm
Length	144 mm
Hole diameter	5.5 mm

Material specifications

Flammability rating according to UL 94	V0 (Interlock)
Seal material	NBR, conductive
Housing material	Die-cast aluminum, salt water resistant
Housing surface material	uncoated
Locking latch material	PA

Mechanical properties

Mechanical data

Type of the screw connection	2x M25
Locking type	Latch

Connection data

Tightening torque	2 Nm ... 3 Nm (for M5 mounting screws on the surface-mount housing)
-------------------	---

Mounting

HC-STA-B24-SLWD-2SSM25-ELC-AL - Housing



1412873

<https://www.phoenixcontact.com/nl/products/1412873>

Assembly note	One opening is sealed with a plastic filler plug and can be opened using a screwdriver.
---------------	---

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66
	IP67
Enclosure rating (NEMA)	4 (UL 50e)
	4X (UL 50e)
	12 (UL 50e)
Impact strength	IK09
Ambient temperature (operation)	-40 °C ... 125 °C

HC-STA-B24-SLWD-2SSM25-ELC-AL - Housing


1412873

<https://www.phoenixcontact.com/nl/products/1412873>



Drawings

Dimensional drawing



Dimensional drawing

HC-STA-B24-SLWD-2SSM25-ELC-AL - Housing



1412873

<https://www.phoenixcontact.com/nl/products/1412873>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/nl/products/1412873>



EAC

Approval ID: RU C-DE.AI30.B.01102



cUL Recognized

Approval ID: E255026



UL Recognized

Approval ID: E255026

DNV

Approval ID: TAE000037S

HC-STA-B24-SLWD-2SSM25-ELC-AL - Housing



1412873

<https://www.phoenixcontact.com/nl/products/1412873>

Classifications

ECLASS

ECLASS-13.0	27440202
ECLASS-15.0	27440202

ETIM

ETIM 10.0	EC000437
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	6,073 kg CO2e
---------	---------------