

1415927
<https://www.phoenixcontact.com/nl/products/1415927>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 3-position, PVC, black RAL 9005, free cable end, on Valve connector B (10 mm), with 1 LED, Wiring: Varistor, cable length: 5 m

Your advantages

- Easy and safe: 100 % electrically tested plug-in components
- Convenient: increased machine availability thanks to quick and easy diagnostics

Commercial data

Item number	1415927
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AF1DCA
Product key	AF1DCA
GTIN	4055626054926
Weight per piece (including packing)	208 g
Weight per piece (excluding packing)	195,6 g
Customs tariff number	85444290
Country of origin	PL

SAC-3P- 5,0-PVC/B-1L-V - Sensor/actuator cable



1415927

<https://www.phoenixcontact.com/nl/products/1415927>

Technical data

Product properties

Application	Standard
Number of positions	3
No. of cable outlets	1
Shielded	no

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	V0
Seal material	TPU
Material housing valve plug	TPU
Contact material	CuSn
Valve plug contact insert material	PA 6.6
Contact surface material	Sn

Electrical properties

Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	24 V AC
	24 V DC
Nominal current I_N	4 A

Valve connector characteristics

Fixing screws	M3 x 29
---------------	---------

Signaling

Status display	1 LED
Status display present	yes

Connector

Connection 1

Type	free cable end
------	----------------

Connection 2

Type	Valve connector B (10 mm)
Number of positions	3
Material	CuSn (Contact)
	Sn (Contact surface)
	PA 6.6 (Contact carrier)
	TPU (Housing)
Protective circuit	Varistor

SAC-3P- 5,0-PVC/B-1L-V - Sensor/actuator cable




1415927

<https://www.phoenixcontact.com/nl/products/1415927>

Cable/line

Cable length	5 m
--------------	-----

PVC black [PVC]

Dimensional drawing	
Cable weight	38.6 kg/km
UL AWM Style	2464
Number of positions	3
Shielded	no
Cable type	PVC black [PVC]
Conductor structure signal line	16x 0.20 mm
AWG signal line	20
Conductor cross-section	3x 0.5 mm ²
Wire diameter incl. insulation	1.5 mm ±0.05 mm
External cable diameter	4.80 mm ±0.2 mm
Outer sheath, material	PVC
External sheath, color	black RAL 9005
Conductor material	Bare Cu litz wires
Material wire insulation	PVC
Single wire, color	black 1, black 2, green/yellow
Overall twist	3 wires, twisted
Max. conductor resistance	39 Ω/km (at 20 °C)
Insulation resistance	≥ 20 MΩ*km
Nominal voltage, cable	300 V
Test voltage	1200 V
Minimum bending radius, fixed installation	5 x D
Smallest bending radius, fixed installation	24 mm
Flame resistance	DIN VDE 0482 DIN EN 50265-2-1
Resistance to oil	in accordance with DIN EN 60811-2-1
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation) -5 °C ... 80 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
----------------------	------

SAC-3P- 5,0-PVC/B-1L-V - Sensor/actuator cable



1415927

<https://www.phoenixcontact.com/nl/products/1415927>

	IP67
Ambient temperature (operation) (Valve connector)	-20 °C ... 85 °C (Valve connector)

Standards and regulations

Valve connector	
Standard designation	Valve connector
Standards/specifications	EN 175301-803

SAC-3P- 5,0-PVC/B-1L-V - Sensor/actuator cable




1415927

<https://www.phoenixcontact.com/nl/products/1415927>


Drawings

Dimensional drawing




Valve connector, type B

Dimensional drawing




Valve connector, type B, side view

Schematic diagram



Valve connector pin assignment, type B



Contact assignment of the valve plug

SAC-3P- 5,0-PVC/B-1L-V - Sensor/actuator cable



1415927

<https://www.phoenixcontact.com/nl/products/1415927>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/nl/products/1415927>



EAC-RoHS
Approval ID: RU D-DE.HB35.B.00387

	CSAus Approval ID: 13631			
	Nominal voltage U _N	Nominal current I _N	Cross section AWG	Cross section mm ²
keine				
	24 V	6 A	-	-

SAC-3P- 5,0-PVC/B-1L-V - Sensor/actuator cable



1415927

<https://www.phoenixcontact.com/nl/products/1415927>

Classifications

ECLASS

ECLASS-13.0	27060312
ECLASS-15.0	27060312

ETIM

ETIM 10.0	EC001855
-----------	----------

UNSPSC

UNSPSC 21.0	31251500
-------------	----------

SAC-3P- 5,0-PVC/B-1L-V - Sensor/actuator cable



1415927

<https://www.phoenixcontact.com/nl/products/1415927>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	2,605 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT B.V.
Hengelder 56 6902 PA Zevenaar
Postbus 246 6900 AE Zevenaar
(0316) 59 17 20
sales@phoenixcontact.nl