

RC-0000000Q0FZ - Housing for circular connector



1592924

<https://www.phoenixcontact.com/nl/products/1592924>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Housing for circular connector, series: RC, straight, M23, Axial O-ring, shielded: yes. This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives.

Commercial data

Item number	1592924
Packing unit	12 pc
Minimum order quantity	12 pc
Sales key	ABRAFK
Product key	ABRAFK
GTIN	4046356193443
Weight per piece (including packing)	94,083 g
Weight per piece (excluding packing)	86,57 g
Customs tariff number	85366990
Country of origin	DE

RC-0000000Q0FZ - Housing for circular connector



1592924

<https://www.phoenixcontact.com/nl/products/1592924>

Technical data

Product properties

Series	RC
Application	Signal
Shielded	yes
Thread type	M23

Material specifications

Material Housing	GD-Zn
Material Housing surface	Ni
Material Rotating parts	CuZn
Gasket and O-ring material	FPM

Connector

Type	straight
------	----------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-20 °C ... 125 °C
Altitude	2000 m

Mounting

Mounting type	Rear mounting
Assembly note	Central fastening


RC-0000000Q0FZ - Housing for circular connector

1592924

<https://www.phoenixcontact.com/nl/products/1592924>



Drawings



Installation dimensions

RC-0000000Q0FZ - Housing for circular connector



1592924

<https://www.phoenixcontact.com/nl/products/1592924>

Classifications

ECLASS

ECLASS-13.0	27440224
ECLASS-15.0	27440224

ETIM

ETIM 10.0	EC003556
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	177b69b4-d108-4925-b243-f9c892028835