

RC-06S1N8K0000 - Contact insert

1606995

<https://www.phoenixcontact.com/nl/products/1606995>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact insert, M23, number of positions: 6, contact connection type: Socket, Crimp connection, series: NC, RC, RM, TU, UC, this item is expected to be lead-free from Q2 2026 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

Commercial data

Item number	1606995
Packing unit	1 pc
Minimum order quantity	10 pc
Sales key	ABRAFU
Product key	ABRAFU
GTIN	4046356199902
Weight per piece (including packing)	12 g
Weight per piece (excluding packing)	5,308 g
Customs tariff number	85389099
Country of origin	DE

RC-06S1N8K0000 - Contact insert

1606995

<https://www.phoenixcontact.com/nl/products/1606995>



Technical data

Product properties

Series	NC
	RC
	RM
	TU
	UC
Application	Signal
Number of positions	6
Connection profile	6
Coding	N
Thread type	M23

Electrical properties

Contact: Contact group 1

Contact diameter	2 mm
Min. cross section	1 mm ²
Max. cross section	1.5 mm ²
Nominal current I _N	20 A (for max. connection cross section)
Nominal voltage U _N	48 V AC
	74 V DC
Overvoltage category	III
Degree of pollution	3
Rated surge voltage	1.5 kV

Connection data

Connection method	Crimp connection
-------------------	------------------

Material specifications

Material Insulating body	PA 6.6
Material Contact	CuZn
Material Contact surface	Ni/Au

Connector

Direction of rotation	Standard
-----------------------	----------

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	50
-----------------------------	----

Environmental and real-life conditions

RC-06S1N8K0000 - Contact insert



1606995

<https://www.phoenixcontact.com/nl/products/1606995>

Ambient conditions

Permissible humidity (storage/transport)
--

50 % ... 65 %

RC-06S1N8K0000 - Contact insert


1606995

<https://www.phoenixcontact.com/nl/products/1606995>



Drawings

Schematic diagram



Connector pin assignment


RC-06S1N8K0000 - Contact insert



1606995

<https://www.phoenixcontact.com/nl/products/1606995>

Schematic diagram



Dimensional drawing

RC-06S1N8K0000 - Contact insert



1606995

<https://www.phoenixcontact.com/nl/products/1606995>

Classifications

ECLASS

ECLASS-13.0	27440223
ECLASS-15.0	27440223

ETIM

ETIM 10.0	EC003557
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

RC-06S1N8K0000 - Contact insert



1606995

<https://www.phoenixcontact.com/nl/products/1606995>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	77211731-05fe-4abd-aa31-4d947f4bbe82

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT B.V.
Hengelder 56 6902 PA Zevenaar
Postbus 246 6900 AE Zevenaar
(0316) 59 17 20
sales@phoenixcontact.nl