

AI-GB 1,5-8 BK-1000 - Ferrule

2100074

<https://www.phoenixcontact.com/nl/products/2100074>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ferrule, Length contact range: 8 mm, sleeve length: 14 mm, color: black

Your advantages

- The ferrules with plastic sleeve are made from soft tin-plated electrolytic copper
- The insulation reliability of close connections is increased and the splicing of wires is prevented

Commercial data

Item number	2100074
Packing unit	1.000 pc
Minimum order quantity	1.000 pc
Sales key	BH341S
Product key	BH341S
GTIN	4067923214064
Weight per piece (including packing)	0,113 g
Weight per piece (excluding packing)	0,113 g
Customs tariff number	85369010
Country of origin	DE

Technical data

Product properties

Conductor category	stranded conductors, class 2, 5, 6 / B, C, K, M
Product property	Suitable for AWG/multi-standard cables due to the increased diameter of the insulating collar
	UL certified
	Made from soft tin-plated electrolytic copper
	Correspond to the requirements of UL 486F
	Plastic collar made of polypropylene
	Halogen-free
	Long/short-term temperature: +105°C/+120°C

Connection data

Conductor connection

Conductor cross-section flexible max.	1.5 mm ²
Conductor cross-section AWG max.	16
Stripping length	11 mm

Dimensions


General

Length [l1]	14 mm
Length (Stripping length)	11 mm

Sleeve

Length [l2]	8 mm
Diameter [d1]	1.7 mm
Strength [s1]	0.15 mm

Plastic collar

Diameter [d2]	3.8 mm
Strength [s2]	1.7 mm
Dimensional drawing	
Sleeve length	14 mm
Length contact range	8 mm
Maximum stripping length	11 mm
Ferrule diameter	1.7 mm
Sleeve wall thickness	0.15 mm
Insulating collar thickness	0.3 mm

AI-GB 1,5-8 BK-1000 - Ferrule



2100074

<https://www.phoenixcontact.com/nl/products/2100074>

Inner dimensions of the insulating collar	3.8 mm
---	--------

Material specifications

Color	black (RAL 9005)
Material	CU-DHP
Flammability rating according to UL 94	HB
Coating	galvanically tin-plated
Surface characteristics	Tin-plated
Components	free from silicone and halogen

Mechanical properties

Technical data


Sleeve length	14 mm
---------------	-------

Standards and regulations

Design according to standard	DIN 46228-4
	UL 486F-E

Drawings

Dimensional drawing



AI-GB 1,5-8 BK-1000 - Ferrule

2100074

<https://www.phoenixcontact.com/nl/products/2100074>



Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/nl/products/2100074>



cULus Listed

Approval ID: E488001

AI-GB 1,5-8 BK-1000 - Ferrule



2100074

<https://www.phoenixcontact.com/nl/products/2100074>

Classifications

ECLASS

ECLASS-13.0	27400201
ECLASS-15.0	27400201

ETIM

ETIM 10.0	EC000005
-----------	----------

UNSPSC

UNSPSC 21.0	27121700
-------------	----------

AI-GB 1,5-8 BK-1000 - Ferrule



2100074

<https://www.phoenixcontact.com/nl/products/2100074>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT B.V.
Hengelder 56 6902 PA Zevenaar
Postbus 246 6900 AE Zevenaar
(0316) 59 17 20
sales@phoenixcontact.nl