

AI 1,5-10 BK-20000 - Ferrule

2100080

<https://www.phoenixcontact.com/nl/products/2100080>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ferrule, Length contact range: 10 mm, sleeve length: 16 mm, color: black

Your advantages

- The ferrules with plastic sleeve are made from soft tin-plated electrolytic copper
- The insulation reliability of close connections is increased and the splicing of wires is prevented

Commercial data

Item number	2100080
Packing unit	20.000 pc
Minimum order quantity	20.000 pc
Sales key	BH3411
Product key	BH3411
GTIN	4067923213890
Weight per piece (including packing)	0,132 g
Weight per piece (excluding packing)	22,22 g
Customs tariff number	85369010
Country of origin	DE

AI 1,5-10 BK-20000 - Ferrule



2100080

<https://www.phoenixcontact.com/nl/products/2100080>

Technical data

Product properties


Conductor category	stranded conductors, class 2, 5, 6 / B, C, K, M
Product property	UL certified
	Made from soft tin-plated electrolytic copper
	Correspond to the requirements of DIN 46228-4 and UL 486F in terms of size
	Plastic collar made of polypropylene
	Halogen-free
	Long/short-term temperature: +105°C/+120°C

Connection data

Conductor connection

Conductor cross-section flexible max.	1.5 mm ²
Conductor cross-section AWG max.	16
Stripping length	13 mm

Dimensions

Dimensional drawing	
Sleeve length	16 mm
Length contact range	10 mm
Maximum stripping length	13 mm
Ferrule diameter	1.7 mm
Sleeve wall thickness	0.15 mm
Insulating collar thickness	0.3 mm
Inner dimensions of the insulating collar	3.4 mm

Material specifications

Color	black (RAL 9005)
Material	CU-DHP
Flammability rating according to UL 94	HB
Coating	galvanically tin-plated
Surface characteristics	Tin-plated
Components	free from silicone and halogen

Mechanical properties

Technical data

Sleeve length	16 mm
---------------	-------

AI 1,5-10 BK-20000 - Ferrule

2100080

<https://www.phoenixcontact.com/nl/products/2100080>




Standards and regulations

Design according to standard	DIN 46228-4
	UL 486F-E

Drawings

Dimensional drawing



Sleeve length (b), length contact range (h), insulating collar inner dimension (d), sleeve diameter (k), insulating collar thickness (i), sleeve wall thickness (j)

AI 1,5-10 BK-20000 - Ferrule

2100080

<https://www.phoenixcontact.com/nl/products/2100080>



Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/nl/products/2100080>



cULus Listed

Approval ID: E488001

AI 1,5-10 BK-20000 - Ferrule



2100080

<https://www.phoenixcontact.com/nl/products/2100080>

Classifications

ECLASS

ECLASS-13.0	27400201
ECLASS-15.0	27400201

ETIM

ETIM 10.0	EC000005
-----------	----------

UNSPSC

UNSPSC 21.0	27121700
-------------	----------

AI 1,5-10 BK-20000 - Ferrule

2100080

<https://www.phoenixcontact.com/nl/products/2100080>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT B.V.
Hengelder 56 6902 PA Zevenaar
Postbus 246 6900 AE Zevenaar
(0316) 59 17 20
sales@phoenixcontact.nl