

CABLE-50/4FLK14/15,0M/YUC - Front adapter



2322773

<https://www.phoenixcontact.com/nl/products/2322773>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cast Yokogawa front adapter with attached round cable and an injection-molded 50-pos. socket strip for the connection of 4 x 8 channels on the field side. Cable length: 15.0 m

Your advantages

- Four 14-pos. connectors on the module side for connecting four 8-channel VARIOFACE modules of the system cabling
- Lateral cable outlet of the I/O module

Commercial data

Item number	2322773
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DK222N
Product key	DK222N
GTIN	4046356450805
Weight per piece (including packing)	2.858,9 g
Weight per piece (excluding packing)	2.858,9 g
Customs tariff number	85444290
Country of origin	DE

CABLE-50/4FLK14/15,0M/YUC - Front adapter



2322773

<https://www.phoenixcontact.com/nl/products/2322773>

Technical data

Electrical properties

Operating voltage (DC)	≤ 30 V DC
Nominal operating mode	100% operating factor
Current (Per path)	≤ 500 mA (uncoiled)

Supported controller: YOKOGAWA CS3000 CentumVP

Suitable I/O card	ADV151
	ADV551

Supported controller: YOKOGAWA STARDOM

Suitable I/O card	NFDV151
	NFDV551

Connection data

Connection 1

Connection in acc. with standard	IEC 60603-13 (in compliance)
Connection method	Yokogawa, I/O cards compatible
Number of connections	1
Number of positions	50
Tightening torque	0.5 Nm (Screw connection)
Insertion/withdrawal cycles	> 50
Pitch	2.54 mm

Connection 2

Connection in acc. with standard	IEC 60603-13 (in compliance)
Connection method	IDC/FLK socket strip
Number of connections	4
Number of positions	14
Insertion/withdrawal cycles	> 50
Pitch	2.54 mm

Dimensions

Cable

Length	15 m
--------	------

Cable/line

50X0.14 [PVC]

UL AWM Style	2464/1061
Number of positions	50
Shielded	yes
Cable type	50X0.14 [PVC]

CABLE-50/4FLK14/15,0M/YUC - Front adapter



2322773

<https://www.phoenixcontact.com/nl/products/2322773>

Conductor type	Assembled shielded round cable
Conductor structure signal line	7x 0.16 mm
AWG signal line	26
Conductor cross-section	50x 0.14 mm ²
Wire diameter incl. insulation	1 mm ±0.03 mm
External cable diameter	11.00 mm ±0.3 mm
Outer sheath, material	Semi-rigid PVC
External sheath, color	gray
Conductor material	Tin-plated Cu litz wires
Cable resistance	≤ 145 Ω/km (at 20 °C)
Insulation resistance	≥ 20 MΩ*km (20 °C)
Smallest bending radius, fixed installation	114 mm
Smallest bending radius, movable installation	205 mm
Dynamic load capacity (bending)	Max. bending cycles: 5000 (at a radius of ≥ 18x outside diameter)
Halogen-free	no
Flame resistance	IEC 60332-1-2 (raw cable)
	VDE 0842, Part 332-1-2 (raw cable)
	IEC 60332-3-22 (raw cable)
	UL VW-1
	CSA FT-1
Resistance to oil	can withstand occasional splashes (raw cable)
Cable type	Splitting cable for four modules

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Degree of protection (Installation location)	≥ IP54 (Installation location)
Ambient temperature (operation) (fixed installation)	-40 °C ... 70 °C (fixed installation)
Ambient temperature (operation) (flexible installation)	-10 °C ... 70 °C (flexible installation)
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	≤ 2000 m

Approvals

UKCA

Certificate	UKCA-compliant
-------------	----------------

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

CABLE-50/4FLK14/15,0M/YUC - Front adapter



2322773

<https://www.phoenixcontact.com/nl/products/2322773>

Drawings

Connection diagram

50-pos. connector to the I/O card	4 x 14-pos. connector to the module		Wire color
1	Byte 0	1	black
3		2	brown
5		3	red
7		4	orange
9		5	yellow
11		6	green
13		7	blue
15		8	Violet
41		9	gray
39		10	White
17	Byte 1	1	white-black
19		2	white-brown
21		3	white-red
23		4	white-orange
25		5	White-yellow
27		6	white-green
29		7	white-blue
31		8	white-violet
43		9	white-gray
37		10	brown-black
2	Byte 2	1	brown-red
4		2	brown-orange
6		3	brown-yellow
8		4	brown-green
10		5	brown-blue
12		6	brown-violet
14		7	brown-gray
16		8	brown-white
42		9	green-black
36		10	green-brown
18	Byte 3	1	green-red
20		2	green-orange
22		3	green-blue
24		4	green-violet
26		5	green-gray
28		6	green-white
30		7	yellow-black
32		8	yellow-brown
44		9	yellow-red
34		10	yellow-orange

CABLE-50/4FLK14/15,0M/YUC - Front adapter



2322773

<https://www.phoenixcontact.com/nl/products/2322773>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/nl/products/2322773>



EAC

Approval ID: RU*-DE.HB*35.B00385



UL Listed

Approval ID: E238705

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	125 V	0.5 A	-	-



cUL Listed

Approval ID: E238705

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	125 V	0.5 A	-	-

CABLE-50/4FLK14/15,0M/YUC - Front adapter



2322773

<https://www.phoenixcontact.com/nl/products/2322773>

Classifications

ECLASS

ECLASS-13.0	27242292
ECLASS-15.0	27242292

ETIM

ETIM 10.0	EC002584
-----------	----------

UNSPSC

UNSPSC 21.0	32151600
-------------	----------

CABLE-50/4FLK14/15,0M/YUC - Front adapter



2322773

<https://www.phoenixcontact.com/nl/products/2322773>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT B.V.
Hengelder 56 6902 PA Zevenaar
Postbus 246 6900 AE Zevenaar
(0316) 59 17 20
sales@phoenixcontact.nl