

UEGM 40/2 BU - Electronics housing



2792604

<https://www.phoenixcontact.com/nl/products/2792604>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Electronic housing, fully equipped with 6 screw connections per side for two PCBs

The figure shows a green version

Commercial data

Item number	2792604
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	ACHCCB
Product key	ACHCCB
GTIN	4017918365318
Weight per piece (including packing)	79,21 g
Weight per piece (excluding packing)	71,086 g
Customs tariff number	85369010
Country of origin	DE

Technical data

Product properties

Housing type	Complete housing
Housing type	Basic housing
Housing series	UEGM
Product family	UEGM 40
Type	Connection system integrated, housing closed
Number of positions	12
Pitch	5 mm
Number of rows	1
Ventilation openings present	no
Pin layout	Linear pinning


Electrical properties

Nominal voltage U_N	500 V (Voltage and current values are affected by the configuration of the printed circuit board.)
Nominal current I_N	10 A

Connection data

Connection method	Screw connection
-------------------	------------------

Dimensions

Dimensional drawing	
Width	40 mm
Height NS 35/7,5	85.5 mm
Depth	79 mm
Length	79 mm
Pitch	5 mm

Material specifications

Color (Housing)	blue (RAL 5015)
Material Housing	PA
Flammability rating according to UL 94	V2

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C
---------------------------------	-------------------

UEGM 40/2 BU - Electronics housing



2792604

<https://www.phoenixcontact.com/nl/products/2792604>

Mounting

Mounting type	DIN rail mounting
Pin layout	Linear pinning

UEGM 40/2 BU - Electronics housing


2792604

<https://www.phoenixcontact.com/nl/products/2792604>



Drawings

Dimensional drawing




UEGM 40/2 BU - Electronics housing


2792604

<https://www.phoenixcontact.com/nl/products/2792604>


Dimensional drawing




Dimensional drawing



Exploded view



Schematic diagram



UEGM 40/2 BU - Electronics housing



2792604

<https://www.phoenixcontact.com/nl/products/2792604>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/nl/products/2792604>

 cULus Recognized Approval ID: E60425-19770427				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
B				
	300 V	10 A	30 - 12	-
D				
	300 V	10 A	30 - 12	-

UEGM 40/2 BU - Electronics housing



2792604

<https://www.phoenixcontact.com/nl/products/2792604>

Classifications

ECLASS

ECLASS-13.0	27190501
ECLASS-15.0	27190501

ETIM

ETIM 9.0	EC001031
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

UEGM 40/2 BU - Electronics housing



2792604

<https://www.phoenixcontact.com/nl/products/2792604>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT B.V.
Hengelder 56 6902 PA Zevenaar
Postbus 246 6900 AE Zevenaar
(0316) 59 17 20
sales@phoenixcontact.nl