

AP 3-TU KS - Cover profile carrier



3034373

<https://www.phoenixcontact.com/nl/products/3034373>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sealable cover profile, for mounting on NS 35/7,5 DIN rail and for fixing the cover profile AP 3, with plastic knurled nut M5, space requirement: 2 mm

Your advantages

- Cover profiles provide protection against unauthorized actuation of terminal strips

Commercial data

Item number	3034373
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE61ZX
Product key	BE61ZX
GTIN	4055626275567
Weight per piece (including packing)	12,53 g
Weight per piece (excluding packing)	12,44 g
Customs tariff number	39269097
Country of origin	DE

AP 3-TU KS - Cover profile carrier


3034373

<https://www.phoenixcontact.com/nl/products/3034373>



Technical data

Dimensions

Dimensional drawing	
Width	2 mm
Height	91 mm
Depth	89 mm
Depth on NS 35/7,5	90.2 mm
Depth on NS 35/15	97.7 mm
Length	91 mm

Material specifications

Color	gray (RAL 7042)
Material	PA
Flammability rating according to UL 94	V0

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

Mounting

Mounting type	NS 32
	NS 35/7,5
	NS 35/15
	NS 35/15-2,3
	NS 35/15 CU

AP 3-TU KS - Cover profile carrier


3034373

<https://www.phoenixcontact.com/nl/products/3034373>



Drawings

Dimensional drawing



AP 3-TU KS - Cover profile carrier



3034373

<https://www.phoenixcontact.com/nl/products/3034373>

Classifications

ECLASS

ECLASS-13.0	27141190
ECLASS-15.0	27250302

ETIM

ETIM 10.0	EC001041
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

AP 3-TU KS - Cover profile carrier

3034373

<https://www.phoenixcontact.com/nl/products/3034373>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0,099 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT B.V.
Hengelder 56 6902 PA Zevenaar
Postbus 246 6900 AE Zevenaar
(0316) 59 17 20
sales@phoenixcontact.nl