

WP-BASE HF 37 - Hose clamp

3240972

<https://www.phoenixcontact.com/nl/products/3240972>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Hose clamp, material: Steel, galvanized, color: black/silver



Commercial data

Item number	3240972
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	AF7DSA
Product key	AF7DSA
GTIN	4046356710909
Weight per piece (including packing)	24,02 g
Weight per piece (excluding packing)	23,442 g
Customs tariff number	39174000
Country of origin	DE

WP-BASE HF 37 - Hose clamp



3240972

<https://www.phoenixcontact.com/nl/products/3240972>

Technical data

Dimensions

Diameter	36 mm
Hole diameter	6.5 mm

Material specifications

Material	Steel, galvanized
Components	halogen-free

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
---------------------------------	-------------------

Mounting

Mounting type	Screw mounting
---------------	----------------

WP-BASE HF 37 - Hose clamp



3240972

<https://www.phoenixcontact.com/nl/products/3240972>

Classifications

ECLASS

ECLASS-13.0	27430315
ECLASS-15.0	27430315

ETIM

ETIM 9.0	EC000799
----------	----------

UNSPSC

UNSPSC 21.0	31162900
-------------	----------

WP-BASE HF 37 - Hose clamp



3240972

<https://www.phoenixcontact.com/nl/products/3240972>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT B.V.
Hengelder 56 6902 PA Zevenaar
Postbus 246 6900 AE Zevenaar
(0316) 59 17 20
sales@phoenixcontact.nl