WP-GT PP HF PG36 - Protective hose screw connection

3241008

https://www.phoenixcontact.com/nl/products/3241008

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable gland made from PP with Pg thread, rotatable, IP54 protection

Commercial data

Item number	3241008
Packing unit	2 pc
Minimum order quantity	2 pc
Sales key	AF7DSA
Product key	AF7DSA
GTIN	4046356711401
Weight per piece (including packing)	37,15 g
Weight per piece (excluding packing)	37,15 g
Customs tariff number	39174000
Country of origin	DE

Technical data

Product properties

Application	Cable gland
Type of the screw connection	Conduit adapter
Cable outlet	straight
Thread type	Pg

Dimensions

Width	59.5 mm
Height	62.5 mm
Wrench size	54 mm
Wrench size for mounting	54 mm

Material specifications

Material	PP
Flammability rating according to UL 94	HB
Material for screw connection	PP
Components	halogen-free

Cable/line

Halogen-free	yes

Mechanical properties

Mechanical data

Type of the screw connection	Conduit adapter

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP54
Ambient temperature (operation)	-10 °C ... 110 °C

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/nl/products/3241008

VDE approval of drawings

Classifications

ECLASS

ECLASS-13.0	27430311
ECLASS-15.0	27430311

ETIM

ETIM 10.0	EC001178

UNSPSC

UNSPSC 21.0	39121300

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

PHOENIX CONTACT B.V.
Hengelder 56 6902 PA Zevenaar
Postbus 246 6900 AE Zevenaar
(0316) 59 17 20
sales@phoenixcontact.nl