



Extract from the online catalog

SACB- 8X0,34/ 3X0,75-50,0 PUR

Order No.: 1503344




<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1503344>

Master cable for sensor/actuator boxes, with PE conductor, unshielded, material PUR/PVC, 11-pos., 8 x 0.34 mm² and 3 x 0.75 mm²

Commercial data	
EAN	4017918896942
Pack	1 pcs.
Customs tariff	85366990
Weight/Piece	5.416 KG
Catalog page information	Page 135 (PC-2009)

Product notes

WEEE/RoHS-compliant since: 05/24/2006



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data	
General data	
Nominal voltage U _N	300 V
Master cable data	
Length of cable	50 m

SACB- 8X0,34/ 3X0,75-50,0 PUR Order No.: 1503344
<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1503344>

Cable type	Master cable suitable for flexible cable conduit
Signal line cross section	8x 0.34 mm ²
AWG signal line	22
Conductor structure, signal line	42x 0.10 mm
Power supply cross section	3x 0.75 mm ²
AWG power supply	19
Conductor structure, voltage supply	96x 0.10 mm
External diameter	9.2 mm
Max. bending cycles	1500000
Bending radius	95 mm
Traversing path	2 m
Traversing rate	2 m/s
Ambient temperature (operation)	-40 °C ... 90 °C (for fixed installation)
	-5 °C ... 80 °C (for flexible installation)

onlinecomponents.com

SACB- 8X0,34/ 3X0,75-50,0 PUR Order No.: 1503344
<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1503344>

Address

PHOENIX CONTACT Deutschland GmbH
Flachmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 12000
Fax +49 5235 3 41200
<http://www.phoenixcontact.de>



© 2010 Phoenix Contact
Technical modifications reserved;

onlinecomponents.com