



Extract from the online catalog

CK1,6-BR-1,50ST AG

Order No.: 1884144



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1884144>

Rolled male contact, taped, silver-plated, 0.5 mm² ... 1.5 mm²

Commercial data	
EAN	4017918163846
Pack	2000 pcs.
Customs tariff	85389099
Weight/Piece	0.00059 KG
Catalog page information	Page 529 (PC-2009)

Product notes

WEEE/RoHS-compliant since:
01/01/2008



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

Electrical characteristics	
Note	For HC-D...R and VC-D...R contact carriers: the quality of a crimp connection is determined by DIN EN 60 352-2
Volume resistance	5 mΩ
Ambient temperature (operation)	-40 °C ... 125 °C

CK1,6-BR-1,50ST AG Order No.: 1884144
<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1884144>

Mechanical characteristics

Conductor cross section	0.5 mm ² ... 1.5 mm ²
Connection cross section AWG	20 ... 16
Stripping length of the individual wire	3.5 mm +1
Insertion/withdrawal cycles	≥ 500

General characteristics

Type	Male contact for taped products
------	---------------------------------

Material data

Contact material	Copper alloy
Contact surface material	hard-silver plated

Certificates / Approvals




Certification

GOST

Drawings

Dimensioned drawing



CK1,6-BR-1,50ST AG Order No.: 1884144
<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1884144>

Address

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 00
Fax +49 5235 3 41200
<http://www.phoenixcontact.de>



© 2009 Phoenix Contact
Technical modifications reserved;

onlinecomponents.com