

## Interruption plug - FIP-3/4 SERVICE - 3069313

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Interruption plug, number of positions: 4, width: 32.6 mm, color: red



RoHS

### Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 157597
GTIN	4055626157597
Weight per Piece (excluding packing)	41.300 g
Custom tariff number	85366990
Country of origin	Poland

### Technical data

#### General

Number of positions	4
Color	red
Insulating material	PA
Flammability rating according to UL 94	V0
Rated surge voltage	4 kV
Test surge voltage	5 kV
Overvoltage category	III
Insulating material group	I
Maximum load current	20 A
Nominal current $I_N$	20 A
Nominal voltage $U_N$	400 V

## Interruption plug - FIP-3/4 SERVICE - 3069313

### Technical data

#### General

Open side panel	Yes
-----------------	-----

#### Dimensions

Width	32.6 mm
Length	53.4 mm
Pitch	8.2 mm

#### Mounting

Mounting type	Insertion in base strip
---------------	-------------------------

#### Standards and Regulations

Flammability rating according to UL 94	V0
--	----


#### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

### Drawings

# Interruption plug - FIP-3/4 SERVICE - 3069313

Circuit diagram



## Classifications

eCl@ss

eCl@ss 10.0.1	27141190
eCl@ss 4.0	27141100
eCl@ss 4.1	27141100
eCl@ss 5.0	27141100
eCl@ss 5.1	27141100
eCl@ss 6.0	27141100
eCl@ss 7.0	27141190

## Interruption plug - FIP-3/4 SERVICE - 3069313

### Classifications

#### eCl@ss

eCl@ss 8.0	27141190
eCl@ss 9.0	27141190

#### ETIM

ETIM 5.0	EC002848
ETIM 6.0	EC002848
ETIM 7.0	EC002848

#### UNSPSC

UNSPSC 13.2	39121410
UNSPSC 18.0	39121410
UNSPSC 19.0	39121410
UNSPSC 20.0	39121410
UNSPSC 21.0	39121410