

## Covering hood - HC-RBO 10 - 3247970

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Covering hood, Length: 144 mm, Width: 41 mm, Height: 33 mm, Color: gray

Image shows HC-RBO 8 version



### Key Commercial Data

Packing unit	1 STK
Minimum order quantity	6 STK
GTIN	 4 046356 586382
GTIN	4046356586382
Weight per Piece (excluding packing)	33.333 g
Custom tariff number	85389099
Country of origin	China

### Technical data

#### General

Color	gray
Material	PA
Flammability rating according to UL 94	V0

#### Dimensions

Width	41 mm
Length	144 mm
Height	33 mm

#### Standards and Regulations

Flammability rating according to UL 94	V0
--	----

# Covering hood - HC-RBO 10 - 3247970

## Technical data

### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

## Classifications

### eCl@ss

eCl@ss 5.1	27141143
eCl@ss 6.0	27379200
eCl@ss 8.0	27379201
eCl@ss 9.0	27379201

### ETIM

ETIM 5.0	EC002498
ETIM 6.0	EC002498

### UNSPSC

UNSPSC 13.2	39121410
-------------	----------

## Approvals

### Approvals

---

Approvals


EAC

---

Ex Approvals

---

### Approval details

EAC		EAC-Zulassung
-----	---	---------------

---