





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT P/N	WEIGHT	SPLIT SLEEVE TYPE
FAP12WAQLCZ	1.28 lb/10 Pcs. (580.6 g/10 Pcs.)	ZIRCONIA
FAP12WBULCZ	1.28 lb/10 Pcs. (580.6 g/10 Pcs.)	ZIRCONIA

NOTES:

- SEE CURRENT CATALOG FOR PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITIES.
- SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
- MATERIALS:
 - PLATE: C.R.S. POWDER COATED
 - ADAPTER: COMPOSITE, AQUA OR BLUE
 - SPLIT SLEEVE: SEE TABLE
- DIMENSIONS IN BRACKETS ARE METRIC.

										12 POSITION SIMPLEX LC FIBER ADAPTER PANEL CUSTOMER DRAWING			
											 PANDUIT TM CORP. TINLEY PARK, ILL 60477		
										 THIRD ANGLE PROJECTION	ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED.		DRAWING FILENAME M01945A0_DC_00A.prt
									DIMENSIONAL TOLERANCES ARE: (.X) (.XXX) ±.010 (0.3) (.XX) ±.03 (0.8) ANGLES		SCALE NONE		
									DRAWN BY MC		REVIEW DRAWING NUMBERS	PART NO. FAP12WAQLCZ FAP12WBULCZ	
									DATE 03-04-05		SEE NOTES	DRAWING NO. 01945-40	SIZE A
R	03-11-05	MC		RELEASED TO PRODUCTION	01945-40								
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH	CHK'D			