



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




PANDUIT P/N	WEIGHT
UICFPSE8***-2G	1.00 LB/10 PCS. (454.4 G/10 PCS.)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.
4. PART INCLUDES:
 - 1- FACEPLATE
 - 2- COLOR COORDINATED LABEL COVER
 - 4- CLEAR LABEL COVER
 - 4- MOUNTING SCREW



MODEL FILENAME M01739BD_UICFPSE82G_01.PRT		SIZE A
DRAWING FILENAME M01739BD_DC_01A.PRT		
MINI-COM™ ULTIMATE ID™ 8 POSITION EXECUTIVE SLOPED DOUBLE GANG FACEPLATE CUSTOMER DRAWING		
 PANDUIT ® TINLEY PARK, IL 60477		1.1. NUMBER N/A
 THIRD ANGLE PROJECTION		PRODUCT SPEC N/A
		WORK INSTRUCTION N/A
		SCALE FULL
DRAWN BY JsP	MATERIAL: ABS	PART NO. UICFPSE8**-2G
DATE 9-18-03		DRAWING NO. 01739-02
CHK'D		

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
R	9-18-03	JsP		RELEASED TO PRODUCTION	01739-02				