


|                                                      |                                                                                                                                                            |
|------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Material                                             | High Conductivity<br>Seamless Copper Tube                                                                                                                  |
| Plating                                              | Electro-Tin                                                                                                                                                |
| Wire Size                                            | 2/0 AWG                                                                                                                                                    |
| Wire Type                                            | Stranded Copper; Class B:<br>Compact, Compressed or<br>Concentric, Class C: Concentric                                                                     |
| Wire Strip Length                                    | 3/4 in.                                                                                                                                                    |
| Stud Size                                            | 5/16 in.                                                                                                                                                   |
| UL Listed Wire<br>Connector                          | Yes, for applications up to 35kv.<br>Consult cable manufacturer for<br>voltage stress relief instructions<br>with applications greater than<br>2000 volts. |
| UL Temperature<br>Rating                             | 90° C                                                                                                                                                      |
| C.S.A Certified<br>Wire Connector                    | Yes                                                                                                                                                        |
| Panduit Color Code<br>on Barrel                      | BLACK                                                                                                                                                      |
| Panduit Die Index No.<br>on Barrel                   | P45                                                                                                                                                        |
| Alternate Industry<br>Die Index No. ( )<br>on Barrel | (13)                                                                                                                                                       |

LISTED  
Wire Connector



|     |      |     |     |             |       |                                                                                                                                  |                                           |
|-----|------|-----|-----|-------------|-------|----------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------|
|     |      |     |     |             |       |  <b>PANGUIT CORP.</b> TINLEY PARK, ILLINOIS |                                           |
|     |      |     |     |             |       | LCAS2/0-56H-X<br>Copper Lug - One-Hole, Short Barrel, 45° Angle Tongue                                                           |                                           |
| 00  | 8/02 | SAB | DRL | RELEASED    | 10325 |                                                                                                                                  |                                           |
| REV | DATE | BY  | CHK | DESCRIPTION | ECN   | SCALE<br>N/A                                                                                                                     | DRAWING NO / CAD FILE<br>LCAS2_0-56H-CUST |