


|                                                      |                                                                                                                                                            |
|------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Material                                             | High Conductivity<br>Seamless Copper Tube                                                                                                                  |
| Plating                                              | Electro-Tin                                                                                                                                                |
| Wire Size                                            | 4/0 AWG                                                                                                                                                    |
| Wire Type                                            | Stranded Copper; Class B:<br>Compact, Compressed or<br>Concentric, Class C: Concentric                                                                     |
| Wire Strip Length                                    | 1-1/4 in.                                                                                                                                                  |
| Stud Size                                            | 3/8 in.                                                                                                                                                    |
| UL Listed Wire<br>Connector                          | Yes, for applications up to 35kv.<br>Consult cable manufacturer for<br>voltage stress relief instructions<br>with applications greater than<br>2000 volts. |
| UL Temperature<br>Rating                             | 90° C                                                                                                                                                      |
| C.S.A Certified<br>Wire Connector                    | Yes                                                                                                                                                        |
| Panduit Color Code<br>on Barrel                      | PURPLE                                                                                                                                                     |
| Panduit Die Index No.<br>on Barrel                   | P54                                                                                                                                                        |
| Alternate Industry<br>Die Index No. ( )<br>on Barrel | (15)                                                                                                                                                       |

LISTED  
Wire Connector



|     |      |     |     |                                   |       |  |                                          |
|-----|------|-----|-----|-----------------------------------|-------|---------------------------------------------------------------------------------------|------------------------------------------|
|     |      |     |     |                                   |       | LCA4/0-38H-X                                                                          |                                          |
|     |      |     |     |                                   |       | Copper Lug - One-Hole, Standard Barrel, 45° Angle Tongue                              |                                          |
| 01  | 3/04 | DRL | DRL | ADDED UL, CSA & PART NO. TO STAMP | 11599 |                                                                                       |                                          |
| REV | DATE | BY  | CHK | DESCRIPTION                       | ECN   | SCALE<br>N/A                                                                          | DRAWING NO / CAD FILE<br>LCA4_0-38H-CUST |