

Material	High Conductivity Seamless Copper Tube
Plating	Electro-Tin
Wire Size	2 AWG
Wire Type	Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric
Wire Strip Length	1-1/4 in.
Stud Size	1/4 in.
UL Listed Wire Connector	Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.
UL Temperature Rating	90° C
C.S.A Certified Wire Connector	Yes
Panduit Color Code on Barrel	BROWN
Panduit Die Index No. on Barrel	P33
Alternate Industry Die Index No. () on Barrel	(10)



Technical drawing of a wire inspection window. The drawing shows a cross-section of a component with a wire inspection window. Key dimensions and features include:

- Wire inspection window:** A horizontal slot with a width of $.10 \pm .01$.
- Beveled wire entry:** A feature on the right side of the window, with a width of $.42 \pm .01$ and a depth of $.31 \pm .01$.
- Dimensions:**
 - $1.16 \pm .04$: Dimension across the top of the beveled wire entry.
 - 1.37 REF: Reference dimension from the bottom of the window to the top of the beveled wire entry.
 - 2.43 REF: Reference dimension from the left edge of the window to the right edge of the beveled wire entry.
 - $45^\circ \pm 5^\circ$: Angle of the beveled wire entry.

						 PANDUIT CORP. TINLEY PARK, ILLINOIS	
00	7/02	SAB	DRL	RELEASED	10341	LCC2-14BWH-Q Copper Lug - Two-Hole, Long Barrel with Window, 45° Angle Tongue	
REV	DATE	BY	CHK	DESCRIPTION	ECN	SCALE N/A	DRAWING NO / CAD FILE LCC2-14BWH-CUST