


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



1. SELECT C28BX040Y1J AS DESIGNATED PART IN PANDUIT LABELING SOFTWARE PROGRAM
 2. INSERT DATA TO BE PRINTED INTO SOFTWARE PROGRAM
 3. INSERT SHEET INTO MANUFACTURED TRAY OF INKJET OR LASER PRINTER.
 4. AFTER PRINTING, REMOVE STRIPS AND INSERT INTO FACEPLATE.
- ADDITIONAL SIZES AVAILABLE FOR A WIDE VARIETY OF COMPONENTS.
FOR TECHNICAL ASSISTANCE CALL: (866)504-5400 EXTENSION 7337

PART NUMBER	MATERIAL	MARKER SIZE inches (mm)	LABELS PER SHEET	SHEETS PER PACKAGE
C28BX040Y1J	GM3S16Y2-925W	2.880 X 0.400	40	25

CAD FILENAME/LAYERS 100472B1_C10168_C28BX040Y1J_00.prt

PANDUIT CORP. TINLEY PARK, ILLINOIS
OPTIMUM LASER/INK JET
WHITE NON-ADHESIVE
LABEL, 2.880 X 0.400

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± .03 (XXX) ± .010
(.XX) ± .03 ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN IN
INCHES, THIRD ANGLE PROJECTION

DRAWN BY

MAT'L:

SCALE

1/2

DATE

SEE TABLE

DRAWING NO.

C10168

DWG

A

SIZE

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
0	9-5-04	JMH		DRAWING RELEASED		R		