


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:


1. SEE SHEET 2 FOR PRODUCT DESCRIPTIONS AND TECHNICAL SPECIFICATIONS.
2. SEE CURRENT CATALOG FOR PATCH CORD LENGTHS AND PACKAGE QUANTITY.
3. FOR LENGTHS OTHER THAN THOSE LISTED IN CATALOG, CONTACT YOUR PANDUIT SALES PERSON.
4. TESTED TO EIA/TIA 568-B.3.
5. PATCH CORD ROUTING CONFIGURATION A TO B.
6. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS, (EUROPEAN DIRECTIVE 2002/95/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
R	06-05-07	MC		RELEASED TO PRODUCTION	02779-38				

SIMPLEX FIBER OPTIC PATCH CORD
SC TO LC CONFIGURATION
CUSTOMER DRAWING



PANDUIT™
CORP.
TINLEY PARK, ILL 60477



ALL DIMENSIONS ARE GIVEN IN INCHES
UNLESS OTHERWISE SPECIFIED.
DIMENSIONAL TOLERANCES ARE:
(.X) ±.03 | (0.8) ANGLES
(.XXX) ±.010 | (0.3)

DRAWING FILENAME
M02779CH_DC_00A.prt
SCALE
NONE

DRAWN BY
MC

REVIEW DRAWING NUMBERS

PART NO.
SEE TABLE, SHT. 2

DATE
05-23-07

CHK'D

DRAWING NO.
02779-38
(SHT. 1 of 2)

SIZE
A



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

SIMPLEX FIBER OPTIC SC TO LC PATCH CORD

PANDUIT PART NO.	CABLE				SC CONNECTOR			LC CONNECTOR		
	RATING	FIBER TYPE	COUNT	COLOR	MAX. IL	RL	COLOR	MAX. IL	RL	COLOR
FXF3-10M*Y	RISER (OFNR)	10GbE 50/125um OM3	SIMPLEX 1.6mm	AQUA	0.30dB	26dB	ELECTRIC IVORY	0.30dB	26dB	ELECTRIC IVORY
F6F3-10M*Y		62.5/125um OM1		ORANGE	0.30dB	20dB	ELECTRIC IVORY	0.30dB	20dB	ELECTRIC IVORY
F9F3-10M*Y		9/125um OS1		YELLOW	0.75dB	55dB	BLUE	0.35dB	55dB	BLUE

* - DENOTES PATCH CORD LENGTH, WHERE M = METERS AND F = FEET

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
R	06-05-07	MC		RELEASED TO PRODUCTION	02779-38				

SIMPLEX FIBER OPTIC PATCH CORD SC TO LC CONFIGURATION CUSTOMER DRAWING									
					PANDUIT ™ CORP. TINLEY PARK, ILL 60477				
					ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ±.03 (.XXX) ±.010 (.3) ±.01 ANGLES				
DRAWN BY MC					REVIEW DRAWING NUMBERS				
DATE 05-23-07					DRAWING FILENAME M02779CH_DC_00A.prt				
CHK'D					SCALE NONE				
					PART NO. SEE TABLE				
					DRAWING NO. 02779-38 (SHT. 2 of 2)				
					SIZE A				