

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


SUPPLIED LABELS

19	20	21	22	23	24
13	14	15	16	17	18
7	8	9	10	11	12
1	2	3	4	5	6



1.25
[31.8]

.62
[15.9]



PANDUIT P/N


WEIGHT

CPPL24M6BLY

6.15 LB/10 PCS
(2789.6 g/10 PCS)

NOTES:

- SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
- SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
- DIMENSIONS IN PARENTHESES ARE IN METRIC.
- PART INCLUDES:
 - 1- METAL STAMPING
 - 4- 6 POSITION FACEPLATE WITH LABEL SLOT
 - 4- LABEL COVER
 - 4- LABEL
 - 1- SCREW KIT (INCLUDES FOUR #12-24 SCREWS)
 - 1- SCREW KIT (INCLUDES FOUR M6 SCREWS)
- LABELS ARE PRE-NUMBERED (1-24) WITH BLANK SIDE FOR CUSTOM LABELING.



NETWORK SYSTEMS

MAY 26 2006

ENGINEERING DEPT

MODEL FILENAME		M00806AC_CPP24M6BL_00.PRT		SIZE A
DRAWING FILENAME		M02479CC_DC56_00A.PRT		
MINI-COM MODULAR 24 PORT M6 FACEPLATE PATCH PANEL WITH LABEL CUSTOMER DRAWING				
 PANDUIT ™ CORP. TINLEY PARK, ILL 60477	I.I. NUMBER		N/A	
	PRODUCT SPEC		N/A	
	WORK INSTRUCTION		N/A	
	SCALE		NONE	
 THIRD ANGLE PROJECTION	ALL DIMENSIONS ARE GIVEN IN INCHES. UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± .010(.3) (.XX) ± .031(.8) ANGLES ±		PART NO. CPPL24M6BLY	
DRAWN BY JsP	MATERIAL PANEL - CRS FACEPLATE - ABS		DRAWING NO. 02479-056	
DATE 4-19-06				

R	4-19-06	JsP	RELEASED TO PRODUCTION	02479-056	MAJ	MAJ				
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH	