



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT P/N	WEIGHT
CNPS	54 LBS/EACH 24.5 Kg/EACH

NOTES:

- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
- PARTS SUPPLIED:
 - 1- SIDE PANEL
 - 1- SET OF MOUNTING BRACKETS
 - 1- MOUNTING HARDWARE KIT
- DIMENSIONS IN PARENTHESIS ARE METRIC.




SIDE PANEL
SUPPORT

DETAIL A


MODEL FILENAME		V10395AY/02.PRT	
CAD FILENAME/LAYERS		V10395AY_DC/02B.PRT	
PANDUIT CORP. TINLEY PARK, ILLINOIS			
SIDE PANEL CUSTOMER DRAWING			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		UNLESS OTHERWISE SPECIFIED,	
INCHES	[METRIC - MILLIMETER]	ANGLE	
X.X +/- 0.06	X. +/- 1.5	ALL DIMENSIONS ARE GIVEN	
X.XX +/- 0.03	X.X +/- 0.8	IN INCHES, THIRD ANGLE PROJECTION.	
X.XXX +/- 0.015	X.XX +/- 0.4		
DRAWN BY JDWE		SCALE NONE	
DATE 1-10-07		DRAWING NO. 10395-26	
CHK'D SJA		SHEET 1 OF 2	
MAT'L:		DWG A SIZE	
SEE NOTES			

02B	4-16-08	LEE		A. ADDED DIMENSIONAL TOLERANCES TO TITLE BLOCK	10395-26					
00	1-10-07	JDWE	SJA	RELEASED TO PRODUCTION	10395-26	SJA	MJM			
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH	

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



FRONT



SIDE

MODEL FILENAME	V10395AY/02.PRT
CAD FILENAME/LAYERS	V10395AY_DC/02B.PRT
PANDUIT CORP. TINLEY PARK, ILLINOIS	
SIDE PANEL CUSTOMER DRAWING	

										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: INCHES X.X +/- 0.06 X.XX +/- 0.03 X.XXX +/- 0.015	[METRIC - MILLIMETER] X +/- 1.5 X.X +/- 0.8 X.XX +/- 0.4	ANGLE +/- 1°	UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.
02B	4-16-08	LEE		SEE SHEET 1 OF 2 FOR REVISIONS	10395-26					DRAWN BY JDWE	SEE NOTES	SCALE NONE	
00	1-10-07	JDWE	SJA	SEE SHEET 1 OF 2 FOR REVISIONS	10395-26	SJA	MJM			DATE 1-10-07		DRAWING NO. 10395-26 SHEET 2 OF 2	DWG A SIZE
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH	CHK'D SJA			