


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




NOTES:

1. SEE CURRENT CATALOG FOR PACKAGE QUANTITY.
2. FOR LENGTHS OTHER THAN THOSE SHOWN, CONTACT YOUR PANDUIT SALES PERSON.
3. TESTED TO EIA/TIA 568-B.3.
4. PATCH CORD ROUTING CONFIGURATION A TO B.

PANDUIT PART NO.	DESCRIPTION	AVAILABLE LENGTHS	
F6Z6P-12M*	62.5/125um OR 50/125um MULTIMODE RISER RATED PATCHCORD FIBER JACK PLUG TO MT-RJ	1, 2, 3, 5, & 10 METER	
F5Z6P-12M*			
COMPONENT	TYPE/DESCRIPTION	COLOR	MAXIMUM LOSS
CABLE	62.5 OR 50/125um 1.8mm ZIPCORD CABLE RISER RATED	ORANGE	
CONNECTORS	OPI-JACK PLUG	ELECTRIC IVORY	.35 dB
	MULTIMODE MT-RJ	BLACK	.35 dB

PANDUIT PART NO.	DESCRIPTION	AVAILABLE LENGTHS	
F6LZ6P-12M*	62.5/125um OR 50/125um MULTIMODE LS-ZH PATCHCORD FIBER JACK PLUG TO MT-RJ	1, 2, 3, 5, & 10 METER	
F5LZ6P-12M*			
COMPONENT	TYPE/DESCRIPTION	COLOR	MAXIMUM LOSS
CABLE	62.5 OR 50/125um 1.8mm ZIPCORD CABLE LOW SMOKE-ZERO HALOGEN	ORANGE	
CONNECTORS	OPI-JACK PLUG	ELECTRIC IVORY	.35 dB
	MULTIMODE MT-RJ	BLACK	.35 dB

												FIBER OPTIC PATCH CORD FIBER JACK PLUG TO MT-RJ CONFIGURATION CUSTOMER DRAWING			
													 TM CORP. TINLEY PARK, ILL 60477		
														ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) (.XXX) ±.010 (0.3) (.XX) ±.03 (0.8) ANGLES	DRAWING FILENAME MO2412BT_DC_00A.prt SCALE NONE
												DRAWN BY MC	REVIEW DRAWING NUMBERS	PART NO. SEE TABLE	
												DATE 11-07-05		DRAWING NO. 02412-08	SIZE A
REV	DATE	BY	CHK	DESCRIPTION		ECN	-	R	CUST	SUP	OTH	CHK'D			