




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
UICFP2S	1.47 LB/10 PCS (668.3g/10 PCS)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.
4. PART INCLUDES:
 - 1- FACEPLATE
 - 2- MOUNTING SCREWS
 - 1- CLEAR SCREW COVER
 - 1- COLOR COORDINATED SCREW COVER
 - 1- CLEAR LABEL COVER



MODEL FILENAME		M02237AA_UICFP2S_01.PRT		SIZE A	
DRAWING FILENAME		M02237AA_DC_01A.PRT			
MINI-COM ULTIMATE ID 2 POSITION STAINLESS STEEL FACEPLATE CUSTOMER DRAWING					
	 CORP. TINLEY PARK, ILL 60477		I.I. NUMBER		N/A
			PRODUCT SPEC		N/A
			WORK INSTRUCTION		N/A
			SCALE		NONE
 THIRD ANGLE PROJECTION		ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± .010(.3) (.XX) ± .031(.8) ANGLES ±			
DRAWN BY JsP		MATERIAL:		PART NO.	
DATE 4-4-07		FACEPLATE- 304 STAINLESS STEEL BACKING- ABS		UICFP2S	
CHK'D				DRAWING NO. 02237-07	

R	4-4-07	JsP		RELEASED TO PRODUCTION	02237-07				
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH