

## Search Results

- Evaluate
  - FAQ's
- Design a Solution
  - Part Drawings
  - PDF-Pre-Terminat ..
- How to Buy
  - Bill of Material
  - Favorite Products List
  - Locate Distributor

## Home > Product On-Line Catalog > Search Results >

Current refinements (click ☐ to remove) Search Tips [?](#)

☒ Text Search: 'F66D3-NM3Y'

Your search criteria matched only one product, shown below

### F66D3-NM3Y



#### Fan-Out Cords – Multimode 62.5/125µm (OM1)

- Pass all TIA/EIA-568-B.3 performance requirements
- Insertion loss per connection: 0.10dB typical; 0.30dB maximum
- Pigtailed (open) end allows quick high performance field fusion splice during installation to provide the lowest installed cost
- 900µm tight-buffered fibers break out to terminated colored buffers for quick and easy identification of separate channels for accurate installations
- Factory terminated and 100% tested for insertion loss
- Insertion loss data recorded for every multimode fan-out cord
- Lifetime traceability of test data to a Q.C. number on each fan-out cord
- Highest quality flame retardant fiber optic cable with tight-buffered coating on each optical fiber

|                                |                                                                                                                                 |
|--------------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| • Part Number                  | F66D3-NM3Y                                                                                                                      |
| • RoHS Compliancy Status       | Intended for use in fixed installations which are outside the scope of RoHS                                                     |
| • Note                         | F66D3-NM3Y replaces F66D3-NM3                                                                                                   |
| • Part Description             | SC to pigtail 6-fiber fan-out cord (six SC connectors on one end and open on the other end on distribution cable) – 62.5/125µm. |
| • Product Type                 | Fan-Out Cords                                                                                                                   |
| • Length (m)                   | 3                                                                                                                               |
| • Fiber Compatibility          | 62.5/125µm                                                                                                                      |
| • Fiber Type                   | Multimode                                                                                                                       |
| • Cable Color                  | Orange                                                                                                                          |
| • Cable Type                   | Duplex                                                                                                                          |
| • CE Compliant                 | No                                                                                                                              |
| • Connector 1 Type             | SC Connector                                                                                                                    |
| • Connector 2 Type             | Pigtail                                                                                                                         |
| • End Configurations           | SC to Pigtail                                                                                                                   |
| • Fiber Count                  | 6                                                                                                                               |
| • Flammability Rating          | Riser (OFNR)                                                                                                                    |
| • Pricing Description          | PC 6-Fiber mm 6 SC-Open 62.5µm 3m                                                                                               |
| • Min. Order UOM               | PC                                                                                                                              |
| • Min. Order Qty.              | 1                                                                                                                               |
| • BOM Qty. (# of Pkgs.)        | <input type="text" value="0"/>                                                                                                  |
| • Add to Favorite Product List | <input type="checkbox"/>                                                                                                        |

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.