



### Search Results

#### Evaluate

- FAQ's

#### Design a Solution

- Catalog Cut Sheet

- PDF-FSTMCXAQ Pro

- PDF-FSCMCXAQ Pro

#### How to Buy

- Bill of Material

- Favorite Products List

- Locate Distributor

## Home > Product On-Line Catalog > Search Results >

Current refinements (click  to remove) Search Tips [?](#)

Text Search: 'FMCBT2EI-X'

Your search criteria matched only one product, shown below

### FMCBT2EI-X



- Allow termination of all *OptiCam*® Connectors (LC, SC and ST) onto 1.6mm - 2.0mm or 3mm jacketed cable
- Color-coded in aqua for *10Gig*™ 50/125µm fiber, black for 50/125µm or 62.5/125µm fiber and blue for singlemode fiber
- Provide mechanical cable retention that consistently meets or exceeds industry standard cable retention
- Require no adhesive, speeding installation
- LC and SC *OptiCam*® Connectors provide non-optical disconnect to maintain data transmission under tensile loads for jacketed cable when terminated using *OptiCam*® Cable Retention Boots

▪ Part Number	FMCBT2EI-X
▪ RoHS Compliancy Status	RoHS directive is not applicable
▪ Part Description	OptiCam® OM1 Multimode 1.6/2.0mm Cable Retention Boot.
▪ Product Type	OptiCam™ 1.6/2.0mm Boots
▪ Color	Electric Ivory
▪ Fiber Cable Size	1.6mm - 2.0mm
▪ Fiber Type	Multimode
▪ Pricing Description	OptiCam 1.6/2.0mm Cable Retention Boot Assemblies (EI) (10 pack)
▪ Min. Order UOM	PC
▪ Min. Order Qty.	10
▪ BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
▪ Add to Favorite Product List	<input type="checkbox"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.